Specifications

Photo is representative

Eaton AHAC-P-1500

Eaton ceiling sensor, Ceiling Sensor, 10-30 VDC from Greengate Switchpack, Maintained closure, White, 40 kHz, Incand, MLV, halo, 1500 sq ft, Occupancy 748813

General specifications	
PRODUCT NAME	Eaton ceiling sensor
CATALOG NUMBER	AHAC-P-1500
UPC	032664748813
PRODUCT LENGTH/DEPTH	4.5 in
PRODUCT HEIGHT	1.42 in
PRODUCT WIDTH	0.8 in
PRODUCT WEIGHT	1 lb
CERTIFICATIONS	NOM cULus Listed
PRODUCT TYPE	Ceiling sensor

Powering Business Worldwide

Product specifications

FREQUENCY RATING	40 kHz
SPECIAL FEATURES	Ceiling Sensor
TYPE	Ceiling sensor
VOLTAGE RATING	10-30 VDC from Greengate Switchpack
SENSOR TYPE	Occupancy
CLOSURE TYPE	Maintained
LOAD TYPE	INC HAL MLV
RANGE	1500 sq ft
COLOR	White

Resources

BROCHURES	Arrow Hart commercial lighting controls brochure Commercial ceiling sensors sell sheet
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - AHAC-P-1500

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.