Specifications

Eaton XBUT35

Eaton XB IEC terminal block, 16 mm Screw connection single level-through-feed, Gray, 8 AWG/6 mm2 maximum wire, IEC 800V, EN 700V, UL 600V, IEC #24-8 AWG, EN #24-8 AWG, UL #24-8 AWG wire, IEC 57A, EN 40,50A, UL 50A

General specifications	
PRODUCT NAME	Eaton XB IEC terminal block
CATALOG NUMBER	XBUT35
UPC	782116905065
PRODUCT LENGTH/DEPTH	2.37 in
PRODUCT HEIGHT	2.88 in
PRODUCT WIDTH	0.63 in
PRODUCT WEIGHT	0.02 lb
WARRANTY	1 year
CERTIFICATIONS	CSA Certified UL Listed

Powering Business Worldwide

Product specifications

TYPE	IEC-XB Series
AMPERAGE RATING	527 (IEC), 40A (EN), 50A (EN), 50A (UL)
VOLTAGE RATING	IEC 800V, EN 700V, UL 600V

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - XBUT35

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.