



Open Switches T&B Catalog Number:

UPC Number:
Status:
Description:

OT40FT3
80432541557
Active

3 pole, 40 amps rated at 600 VAC, UL 508, door mounted open non-fusible disconnect switch

Features

Quick make, quick brake mechanism
Extremely compact size
Finger-proof construction with no hazardous exposed parts

Application

Industrial control panel disconnects
For use in motor controller and motor overload protection applications
Can be used as an OSHA lockout/tagout disconnect

General

Style	Door Mounted
Number of Poles	3
Series	Non-fusible

Approvals

UL Class	UL 508
----------	--------

Dimension Information

H x W x D (inches)	2.13 x 1.69 x 2.64
--------------------	--------------------

Specifications

Rated Current (Amps)	40
Rated Voltage AC	600

Packaging

T&B Inner Pack	1
Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	0.23 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com



Open Switches
T&B Catalog Number:

OT40FT3
 80432541557
 Active

UPC Number:
Status:
Description:

3 pole, 40 amps rated at 600 VAC, UL 508, door mounted open non-fusible disconnect switch

Features

- Quick make, quick brake mechanism
- Extremely compact size
- Finger-proof construction with no hazardous exposed parts

Application

- Industrial control panel disconnects
- For use in motor controller and motor overload protection applications
- Can be used as an OSHA lockout/tagout disconnect

General

Style	Door Mounted
Number of Poles	3
Series	Non-fusible

Approvals

UL Class	UL 508
----------	--------

Dimension Information

H x W x D (inches)	2.13 x 1.69 x 2.64
--------------------	--------------------

Specifications

Rated Current (Amps)	40
Rated Voltage AC	600

Packaging

T&B Inner Pack	1
Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	0.23 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com