

# TYPE 1 ENCLOSURES



## Screw Cover – Powder Coated

- Designed for use as junction and pull boxes
- Stock inventory sizes from 4x4x4 to 48x48x18
- Custom sizes and modifications available

### SPECIFICATIONS

- Manufactured from code gauge, low carbon steel
- Covers feature keyhole slots which allow the plated screws to stay in place and make for easy installation
- Embossed grounding provision on sizes up to 24x24x12
- Holes are incorporated into the back of enclosure for easy mounting
- Available with or without knockouts

### FINISH

- Standard: Gunsmoke Gray Powder Coated
- Optional powder coat colors and custom silkscreen printing available (see pg. 48)

### INDUSTRY STANDARDS

- Type 1 - UL 50 and UL 50E: Intended for indoor use primarily to provide a degree of protection against limited amounts of falling dirt.
- RoHS compliant

### ACCESSORIES



Replacement Screw Cover Lid – Powder Coated



Flush Cover Lid – Powder Coated

CATALOG NUMBER	UPC (761515)	SIZE (W"xH"xD")	WGT	LIST PRICE	SCREW COVER	LIST PRICE	FLUSH COVER	LIST PRICE
444SC	22010	4x4x4	1	\$17.78	44SC	\$8.89	44FC	\$8.89
664SC	22130	6x6x4	3	\$20.00	66SC	\$9.95	66FC	\$9.95
666SC	22140	6x6x6	3	\$25.56	66SC	\$9.95	66FC	\$9.95
684SC	22160	6x8x4	3	\$26.67	68SC	\$10.00	68FC	\$10.00
6124SC	22166	6x12x4	5	\$35.56	612SC	\$14.89	612FC	\$14.89
884SC	22280	8x8x4	4	\$31.11	88SC	\$12.22	88FC	\$12.22
886SC	22290	8x8x6	5	\$35.56	88SC	\$12.22	88FC	\$12.22
8104SC	22320	8x10x4	5	\$33.33	810SC	\$14.44	810FC	\$14.44
8124SC	22360	8x12x4	6	\$37.78	812SC	\$14.89	812FC	\$14.89
10104SC	22430	10x10x4	6	\$37.78	1010SC	\$15.55	1010FC	\$15.55
10106SC	22440	10x10x6	7	\$46.67	1010SC	\$15.55	1010FC	\$15.55
12124SC	22580	12x12x4	8	\$47.78	1212SC	\$21.11	1212FC	\$21.11
12126SC	22590	12x12x6	10	\$60.00	1212SC	\$21.11	1212FC	\$21.11
12184SC	22700	12x18x4	11	\$73.33	1218SC	\$25.78	1218FC	\$25.78
12186SC	22710	12x18x6	14	\$84.44	1218SC	\$25.78	1218FC	\$25.78
444SCNK	22012	4x4x4	1	\$17.78	44SC	\$8.89	44FC	\$8.89
664SCNK	22132	6x6x4	3	\$20.00	66SC	\$9.95	66FC	\$9.95
666SCNK	22142	6x6x6	3	\$25.56	66SC	\$9.95	66FC	\$9.95
884SCNK	22282	8x8x4	4	\$31.11	88SC	\$12.22	88FC	\$12.22
886SCNK	22292	8x8x6	5	\$35.56	88SC	\$12.22	88FC	\$12.22
888SCNK	22300	8x8x8	6	\$57.78	88SC	\$12.22	88FC	\$12.22
10104SCNK	22432	10x10x4	6	\$37.78	1010SC	\$15.55	1010FC	\$15.55
10106SCNK	22442	10x10x6	7	\$46.67	1010SC	\$15.55	1010FC	\$15.55
12124SCNK	22582	12x12x4	8	\$47.78	1212SC	\$21.11	1212FC	\$21.11
12126SCNK	22592	12x12x6	10	\$60.00	1212SC	\$21.11	1212FC	\$21.11
12128SCNK	22600	12x12x8	11	\$80.00	1212SC	\$21.11	1212FC	\$21.11
121210SCNK	22610	12x12x10	13	\$111.11	1212SC	\$21.11	1212FC	\$21.11
121212SCNK	22620	12x12x12	15	\$133.33	1212SC	\$21.11	1212FC	\$21.11
16164SCNK	22940	16x16x4	12	\$84.18	1616SC	\$27.78	1616FC	\$27.78
16166SCNK	22950	16x16x6	14	\$97.78	1616SC	\$27.78	1616FC	\$27.78
18184SCNK	23020	18x18x4	16	\$96.67	1818SC	\$28.89	1818FC	\$28.89
18186SCNK	23030	18x18x6	19	\$106.67	1818SC	\$28.89	1818FC	\$28.89
18188SCNK	23040	18x18x8	20	\$133.33	1818SC	\$28.89	1818FC	\$28.89
181810SCNK	23050	18x18x10	23	\$186.67	1818SC	\$28.89	1818FC	\$28.89
181812SCNK	23060	18x18x12	25	\$186.67	1818SC	\$28.89	1818FC	\$28.89
18246SCNK	23100	18x24x6	24	\$194.44	1824SC	\$40.00	1824FC	\$40.00
24244SCNK	23290	24x24x4	27	\$231.11	2424SC	\$45.56	2424FC	\$45.56
24246SCNK	23300	24x24x6	30	\$222.22	2424SC	\$45.56	2424FC	\$45.56
24248SCNK	23310	24x24x8	34	\$248.89	2424SC	\$45.56	2424FC	\$45.56
242410SCNK	23320	24x24x10	38	\$346.67	2424SC	\$45.56	2424FC	\$45.56
242412SCNK	23330	24x24x12	44	\$355.56	2424SC	\$45.56	2424FC	\$45.56
30306SCNK	23340	30x30x6	45	\$533.33	3030SC	\$137.24	3030FC	\$137.24
30308SCNK	23480	30x30x8	51	\$533.33	3030SC	\$137.24	3030FC	\$137.24
303010SCNK	23530	30x30x10	55	\$555.56	3030SC	\$137.24	3030FC	\$137.24
303012SCNK	23580	30x30x12	65	\$555.56	3030SC	\$137.24	3030FC	\$137.24
36366SCNK	23440	36x36x6	60	\$533.33	3636SC	\$225.92	3636FC	\$225.92
36368SCNK	23500	36x36x8	78	\$553.33	3636SC	\$225.92	3636FC	\$225.92
363610SCNK	23550	36x36x10	79	\$711.11	3636SC	\$225.92	3636FC	\$225.92
363612SCNK	23600	36x36x12	87	\$711.11	3636SC	\$225.92	3636FC	\$225.92
363618SCNK	23602	36x36x18	150	\$1,300.00	3636SC	\$225.92	3636FC	\$225.92
48488SCNK	23505	48x48x8	195	\$1,502.22	4848SC	\$300.00	n/a	n/a
484812SCNK	23605	48x48x12	220	\$1,274.76	4848SC	\$300.00	n/a	n/a
484818SCNK	23610	48x48x18	276	\$1,808.00	4848SC	\$300.00	n/a	n/a



TYPE 1 ENCLOSURES  
TYPE 3 AND 3R ENCLOSURES  
CABLE MANAGEMENT SOLUTIONS  
UTILITY AND STORAGE CABINETS  
HARDWARE AND ACCESSORIES  
CUSTOM ENCLOSURE SOLUTIONS