



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



10250T10153 Flush PB BK 1no *Eaton Corp*

Catalog Number	10250T10153
Manufacturer	Eaton Corp
Description	Eaton, 30.5 MM, Heavy-Duty Watertight/Oiltight Pushbutton, Class I Division 2, Black, Plastic Actuator, Chrome Bezel, 1NO, Non-Illuminated, Flush Mounting, Momentary, 30.5 MM, Flush Pushbutton, 10250T Series
Weight per unit	0.4000 (lbs/each)
Product Category	Push Button Complete Assemblie

Features

action	Black
Contact Configuration	1 NO
media	Yes

Dimensions and Weight

Depth	2.25
Height	1.75
Size	30.5 MM
Width	1.8

Descriptions

Description	FLUSH PB BK 1NO
extra long description	ETN 10250T101-53 FLUSH PB BK 1NO
Features	Eaton's 10250T line of 30.5 mm pushbuttons features a heavy-duty zinc die cast construction. Reliability nibs improve contact reliability even under dry circuit and fine dust conditions. In addition, drainage holes prevent the buildup of liquid inside the operator, which can prevent operation in freezing environments.
Long Description	Eaton, 30.5 mm, Heavy-Duty Watertight/Oiltight Pushbutton,Class I Division 2,Black,Plastic Actuator,Chrome bezel,1NO,Non-Illuminated,Flush mounting,Momentary,30.5 mm,Flush Pushbutton,10250T Series
Product Type	Flush PB BK 1no

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113258836
Manufacturers Part Number	10250T101-53
Model	Pushbutton
UPC	782113258836



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description OILTIGHT OPERATORS.30MM

Packaging

Carton 1

Weight Per each 0.4

Uses, Certifications, and Standards

Application Stationary Machinery and Equipment Outside Factory -
..... Stationary Machinery and Equipment Outside Factory - Other

Mounting FLUSH

standard CSA Certified,UL Listed,CE Marked