



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



10250T297LGP2A Pretest FV 120VAC Green Led - Plastic Lens

Eaton Corp

Catalog Number	10250T297LGP2A
Manufacturer	Eaton Corp
Description	Eaton 10250T Pushbutton, Heavy-Duty Watertight and Oiltight Indicating Light, Heavy-Duty Watertight and Oiltight, Pretest, Led, Full Voltage, Nema 3, 3R, 4, 4X, 12, 13, Green, Plastic, 120 V, 30.5 MM
Weight per unit	0.4000 (lbs/each)
Product Category	Pilot Light Complete Assemblie

Features

dimensions	2.6000 IN X 2.2000 IN X 4.7000 IN
media	Yes

Material, Color, and Finish

Style	30.5 mm
-------	---------

Descriptions

Description	PRESTEST FV 120VAC GREEN LED - PLASTIC LENS
extra long description	ETN 10250T297LGP2A PRESTEST FV 120V
Features	Eaton's 10250T line of 30.5 mm pushbuttons features a heavy-duty zinc die cast construction. Reliability nibs improve contact reliability even under dry circuit and fine dust conditions. In addition, drainage holes prevent the buildup of liquid inside the operator, which can prevent operation in freezing environments.
Long Description	Eaton 10250T pushbutton, Heavy-duty watertight and oiltight Indicating Light, Heavy-duty watertight and oiltight, PresTest, LED, Full voltage, NEMA 3, 3R, 4, 4X, 12, 13, Green, Plastic, 120 V, 30.5 mm
Product Type	Pretest FV 120VAC GN Led-Plastic Lens

Manufacturer Information

Brand	Eaton
GTIN	00782114712580
Manufacturers Part Number	10250T297LGP2A
UPC	782114712580

Taxonomies, Classifications, and Categories

Category Description	OILTIGHT OPERATORS.30MM
Type	PUSHBUTTON

Packaging

Carton	1
Weight Per each	0.4



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & EOEM - Electrical Assemblies, Panels
and EOEMs

standard

UL Listed, CSA Certified, CE Marked