



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



10250T22KB Sel SW 3P BK KNB 2NO 2NC

Eaton Corp

Catalog Number	10250T22KB
Manufacturer	Eaton Corp
Description	Eaton 10250T Pushbutton, Heavy-Duty Assembled Selector Switch, 10250T, 60° Throw, Nema 3, 3R, 4, 4X, 12, 13, Non-Illuminated, Three-Position, Knob, Black Actuator, 2NO-2NC
Weight per unit	0.3500 (lbs/each)
Product Category	Selector Switch Complete Assem

Features

actuator	Knob
Contact Configuration	2 NO-2 NC
dimensions	2.6000 IN X 2.2000 IN X 4.7000 IN
media	Yes

Dimensions and Weight

Size	30.5 MM
------	---------

Descriptions

Description	SEL SW 3P BK KNB 2NO 2NC
extra long description	ETN 10250T22KB Selector Switch Bla
Features	Eaton's 10250T line of 30.5 mm pushbuttons features a heavy-duty zinc die cast construction. Reliability nibs improve contact reliability even under dry circuit and fine dust conditions. In addition, drainage holes prevent the buildup of liquid inside the operator, which can prevent operation in freezing environments.
Long Description	Eaton 10250T pushbutton, Heavy-Duty Assembled Selector Switch, 10250T, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Three-position, Knob, Black actuator, 2NO-2NC
Product Type	Selector Switch Black 3POS KNB 2NO 2NC

Manufacturer Information

Brand	Eaton
GTIN	00782113358260
Manufacturers Part Number	10250T22KB
UPC	782113358260

Taxonomies, Classifications, and Categories

Category Description	OILTIGHT OPERATORS.30MM
Type	PUSHBUTTON



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.35

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Power Distribution and ControlElec Assemblies, Panels & EOEM - Electrical Assemblies and EOEMs - Other
standard	UL Listed,CSA Certified,CE Marked