



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

110 Success Blvd  
79029-0000, TX Dumas  
Phone: 806-934-4805  
Fax: 806-717-2052



## 11100RQD03 Ac/DC Right Angle Thru Beam Source Wide Angle With *Eaton Corp*

|                  |                                                                                                                                              |
|------------------|----------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | 11100RQD03                                                                                                                                   |
| Manufacturer     | Eaton Corp                                                                                                                                   |
| Description      | Eaton Comet 18MM Tubular Photoelectric Sensor, Through Beam, Right Angle, Power, Dual Key Micro, 4 Pin, 20-264 Vac 50/60 HZ, 15-30 VDC (NPN) |
| Weight per unit  | 0.7000 (lbs/each)                                                                                                                            |
| Product Category | Sensor Accessories                                                                                                                           |

### Features

|            |                |
|------------|----------------|
| connection | Dual key micro |
|------------|----------------|

### Dimensions and Weight

|        |      |
|--------|------|
| Height | 0.71 |
| Length | 2.55 |
| Width  | 0.47 |

### Descriptions

|                        |                                                                                                                                                                                     |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description            | AC/DC RIGHT ANGLE THRU BEAM SOURCE WIDE ANGLE WITH                                                                                                                                  |
| extra long description | ETN 11100RQD03 18MM TB SOURCE RA,20                                                                                                                                                 |
| Features               | Eaton's Comet Series Photoelectric Sensors is a complete line of high performance, 18 mm tubular sensors with a variety of models and modes to solve virtually any sensing problem. |
| Long Description       | Eaton Comet 18mm tubular photoelectric sensor,Through Beam, Right Angle, Power, Dual key micro, 4 pin, 20-264 Vac 50/60 Hz, 15-30 Vdc (NPN)                                         |
| Product Type           | 18MM TB Source Ra, 20-264VACDC, Micro Conn                                                                                                                                          |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00782113843377 |
| Manufacturers Part Number | 11100RQD03     |
| UPC                       | 782113843377   |

### Taxonomies, Classifications, and Categories

|                      |                                               |
|----------------------|-----------------------------------------------|
| Category Description | Miscellaneous commercial & industrial devices |
| Type                 | Tubular photoelectric sensor                  |

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Weight Per each | 0.7 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

110 Success Blvd  
79029-0000, TX Dumas  
Phone: 806-934-4805  
Fax: 806-717-2052

## Uses, Certifications, and Standards

|                       |                                             |
|-----------------------|---------------------------------------------|
| Application           | Vehicles: On-Road - PickUp & Delivery: Food |
| Operating Temperature | -4° to 158°F (-20° to 70°C)                 |
| standard              | cUL Recognized,UL Recognized                |