



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2830 Global Pkwy
73110-0000, OK Midwest City
Phone: 405-622-4254
Fax: 405-622-4255



12100RQD03 Ac/DC Right Angle Thru Beam Detector Wide Angle Wi *Eaton Corp*

Catalog Number	12100RQD03
Manufacturer	Eaton Corp
Description	Eaton Comet 18MM Tubular Photoelectric Sensor, Through Beam, Right Angle, Output On, Dual Key Micro, 300 Ma Ac/DC At 20-264 Vac/15-30 VDC, 4 Pin, Ac: L1 Switched, DC: NPN Open Collector, 20-264 Vac 50/60 HZ, 15-30 VDC (NPN)
Weight per unit	0.5000 (lbs/each)
Product Category	Sensor Accessories

Features

connection	Dual key micro
------------	----------------

Dimensions and Weight

Height	0.71
Length	2.55
Width	0.47

Descriptions

Description	AC/DC RIGHT ANGLE THRU BEAM DETECTOR WIDE ANGLE WI
extra long description	ETN 12100RQD03 ACDC RT ANG TB DETEC
Features	Eaton's Comet Series Photoelectric Sensors is a complete line of high performance, 18 mm tubular sensors with a variety of models and modes to solve virtually any sensing problem.
Long Description	Eaton Comet 18mm tubular photoelectric sensor, Through Beam, Right Angle, Output ON, Dual key micro, 300 mA AC/DC at 20-264 Vac/15-30 Vdc, 4 pin, AC: L1 switched, DC: NPN open collector, 20-264 Vac 50/60 Hz, 15-30 Vdc (NPN)
Product Type	Acadc RT Ang TB Detector, Wide Ang W/

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113843452
Manufacturers Part Number	12100RQD03
UPC	782113843452

Taxonomies, Classifications, and Categories

Category Description	SENSORS
Type	Tubular photoelectric sensor

Packaging

Carton	1
Weight Per each	0.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2830 Global Pkwy
73110-0000, OK Midwest City
Phone: 405-622-4254
Fax: 405-622-4255

Uses, Certifications, and Standards

Application	Vehicles: On-Road - PickUp & Delivery: Food
Operating Temperature	-4° to 158°F (-20° to 70°C)
standard	cUL Recognized,UL Recognized