




Catalog Number: 121272-GSC1-NK
Item Description: N1 SCREW CVR GUTTER NK
UPC Code: 784572101500

Brand Name: Milbank
Type: Lay In Wireway
Application: Wireway
Standard: UL Listed, Type 1
Cover Type: Screw Cover
Enclosure: Indoor Enclosure
Nominal Cross Section: 12x12
Straight Section Length: 72
Material: Steel with Powder Coat Finish
Finish: ANSI 61 Gray
Knockouts: False




Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

ITEM	QTY.	PART NUMBER	DESCRIPTION
1	1	(SEE CHART)	BACK
2	2	(SEE CHART)	PLATE/COVER
3	1	1002943	LABEL (U/L LISTING)
4	1	1002923	LABEL, RATING
5	8	1001290	SCREW, 10-32 X 5/16
6	4	1002880	BAG ASSY.



SUFFIX	BACK #	COVER #
-SU	1129284	1011834
-SUC	1129285	1101789
-SO	1096769	1099488
-SUNK	1010739	1011834
-NK	1010737	1099488
-SUNKC	1129286	1101789



SUFFIX	FINISH
NONE	PAINTED
-NP	NOT PAINTED

NOTE:
 1. PLACE BAG ASSY INSIDE ENCLOSURE. (NOT SHOWN)
 2. WHEN SOLD AS (RC)- PREFIX USE LABEL #1125051 INSTEAD OF #1002943.

Material:	14 GA. - SEE CHART		General Offices: Kansas City, MO	
Finish:	SEE CHART		Title:	SCREW COVER WIREWAY 12 x 12 x 72, TYPE 1 NEMA ENCLOSURE
Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X" ±2°			Catalog No.:	121272-GSC1
		Projection	Customer:	MILBANK STANDARD
Scale:	NTS	Checked By:	Drawing No.:	554-11
Drawn By:	DY	Approved By:	Date:	Sheet 1 of 1

D	8-30-07	REMOVED IT. 1002923 & ADDED IT. 1099488	ECO. 15946	DL
		& IT. 1001290 QTY. W & ADDED BACK & COVER CHART		




Catalog Number: 121272-GSC1-NK
Item Description: N1 SCREW CVR GUTTER NK
UPC Code: 784572101500

Brand Name: Milbank
Type: Lay In Wireway
Application: Wireway
Standard: UL Listed, Type 1
Cover Type: Screw Cover
Enclosure: Indoor Enclosure
Nominal Cross Section: 12x12
Straight Section Length: 72
Material: Steel with Powder Coat Finish
Finish: ANSI 61 Gray
Knockouts: False




Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

ITEM	QTY.	PART NUMBER	DESCRIPTION
1	1	(SEE CHART)	BACK
2	2	(SEE CHART)	PLATE/COVER
3	1	1002943	LABEL (U/L LISTING)
4	1	1002923	LABEL, RATING
5	8	1001290	SCREW, 10-32 X 5/16
6	4	1002880	BAG ASSY.



SUFFIX	BACK #	COVER #
-SU	1129284	1011834
-SUC	1129285	1101789
-SO	1096769	1099488
-SUNK	1010739	1011834
-NK	1010737	1099488
-SUNKC	1129286	1101789



SUFFIX	FINISH
NONE	PAINTED
-NP	NOT PAINTED

NOTE:
 1. PLACE BAG ASSY INSIDE ENCLOSURE. (NOT SHOWN)
 2. WHEN SOLD AS (RC)- PREFIX USE LABEL #1125051 INSTEAD OF #1002943.

Material:	14 GA. - SEE CHART		General Offices: Kansas City, MO	
Finish:	SEE CHART		Title:	SCREW COVER WIREWAY 12 x 12 x 72, TYPE 1 NEMA ENCLOSURE
Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X" ±2"			Catalog No.:	121272-GSC1
		Projection	Customer:	MILBANK STANDARD
Scale:	NTS	Checked By:	Drawing No.:	554-11
Drawn By:	DY	Approved By:	Date:	Sheet 1 of 1

D	8-30-07	REMOVED IT. 1002923 & ADDED IT. 1099488	ECO. 15946	DL
		& IT. 1001290 QTY. W & ADDED BACK & COVER CHART		