



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



121272GRTNK 12X12X72 RT Wireway

Unity MFG

| | |
|------------------|---|
| Catalog Number | 121272GRTNK |
| Manufacturer | Unity MFG |
| Description | Unity 121272GRTNK GRT Gutter Slip-On Cover Wiring Trough, Width: 12 In, 12 In Depth, Length: 72 In, 14 Ga Low Carbon Steel, Gray Polyester Powder Thermoset Over Phosphatized Surface, Nema 3R, IP32 Enclosure, Gunsmoke Gray Color, No Knockouts, UI 50 and UI 870 - Type 3R: Intended For Outdoor Use Primarily to Provide A Degree Of Protection Against Rain, Sleet and Damage From External Ice Formation, Csa C22.2 No. 26 Certified, Type 3R, IEC 60529, Rohs Compliant, For Cable and Wire Junction, Distribution and T |
| Weight per unit | 70.0 (lbs/each) |
| Product Category | Nema Type 3R Trough & Gutter |

Features

| | |
|-----------|------------------|
| Knockouts | NO |
| Material | Low-Carbon Steel |

Material, Color, and Finish

| | |
|--------|------------------|
| Color | Gray |
| Finish | POLYESTER POWDER |

Dimensions and Weight

| | |
|--------|----|
| Depth | 12 |
| Length | 72 |
| Width | 12 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 12X12X72 RT WIREWAY |
| extra long description | UNT 121272GRTNK N3R SCREW COVER GUT |
| Long Description | Unity 121272GRTNK GRT Gutter Slip-On Cover Wiring Trough, Width: 12 IN, 12 IN Depth, Length: 72 IN, 14 GA Low Carbon Steel, Gray Polyester Powder Thermoset Over Phosphatized Surface, NEMA 3R, IP32 Enclosure, Gunsmoke Gray Color, No Knockouts, UL 50 And UL 870 - Type 3R: Intended For Outdoor Use Primarily To Provide A Degree Of Protection Against Rain, Sleet And Damage From External Ice Formation, CSA C22.2 No. 26 Certified, Type 3R, IEC 60529, RoHS Compliant, For Cable And Wire Junction, Distribution And T |
| Product Type | N3R Screw Cover Gutter No K.O. Powder Coated |
| Special Features | For protecting wiring indoors from dripping water, or outdoors from rain, sleet and snow; Formed from code gauge, low carbon steel; Drip shield top, seam-free sides; Accumulation-free bottom; Embossed mounting holes provided; Slip-on cover without gasket |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Unity |
| GTIN | 00761515144961 |
| Manufacturers Part Number | 121272GRTNK |
| UPC | 761515144961 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | STEEL WIRE WAY JUNCTION BOXES |
| Type | GRT Gutter Slip-On Cover Wiring Trough |

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight Per each | 70 |

Uses, Certifications, and Standards

| | |
|--------------------|--|
| Application | For Cable And Wire Junction, Distribution And Termination, Houses Runs Of Control And Power Cable |
| Enclosure standard | NEMA 3R, IP32 UL 50 And UL 870 - Type 3R: Intended For Outdoor Use Primarily To Provide A Degree Of Protection Against Rain, Sleet And Damage From External Ice Formation, CSA C22.2 No. 26 Certified, Type 3R, IEC 60529, RoHS Compliant |