



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



122 1/4-20 Beam Clamp 50-PK

Topaz - Southwire LLC

Catalog Number	122
Manufacturer	Topaz - Southwire LLC
Description	Beam Clamp, Single U Type; Malleable Iron Material; 3/4 Inch Max. Jaw Capacity; 125 LB Load Capacity; 1/4 Inch-20 Tpi Screw Size; Square Head Screw Type; Yes Supplied With Screw; Size 1.39 Inch L X 1.13 Inch W X 1.4 Inch H
Weight per unit	0.1830 (lbs/each)
Product Category	Anchors & Fasteners

Features

Load Capacity	125 Lb
Material	Malleable Iron
Maximum Jaw Capacity	3/4 INCH
Screw Size	1/4 INCH-20 TPI
Screw Type	Square Head
Supplied with Screw	YES

Descriptions

Additional Information	Size 1.39 Inch L x 1.13 Inch W x 1.4 Inch H
Commodity Description	ANCHORS & FASTENERS
Description	1/4-20 BEAM CLAMP 50-PK
extra long description	1-SCREW, 2-HOLE TYPE; MALLEABLE IRON MATERIAL; ZINC PLATED FINISH; 3/4 INCH MAX. JAW CAPACITY; SUPPORTS THREADED ROD, THREADED BRINDLE RINGS AND ELECTRICAL BOXES APPLICATION; 125 POUND LOAD CAPACITY; 1/4 INCH-20 TPI SCREW SIZE; SQUARE HEAD SCREW TYPE; YES SUPPLIED WITH SCREW; ROHS COMPLIANT; OVERALL DIMENSION 1.13 INCH LENGTH X 1.4 INCH WIDTH X 1.39 INCH HEIGHT; TIGHTEN TORQUE 60 INCH
Long Description	BEAM CLAMP, SINGLE U TYPE; MALLEABLE IRON MATERIAL; 3/4 INCH MAX. JAW CAPACITY; 125 LB LOAD CAPACITY; 1/4 INCH-20 TPI SCREW SIZE; SQUARE HEAD SCREW TYPE; YES SUPPLIED WITH SCREW; SIZE 1.39 INCH L X 1.13 INCH W X 1.4 INCH H
Product Type	Beam Clamp

Manufacturer Information

Brand	Southwire Rough Electrical Com
GTIN	00751338107106
UPC	751338107106



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	SINGLE U

Packaging

Carton	1
Package	50
Weight Per each	0.183