



**P&S** Floor Boxes

YOUR COMPLETE LINE OF RUGGED,  
EASY-TO-INSTALL SOLUTIONS.

 **legrand**<sup>®</sup>

---

**Pass & Seymour**

designed to be better.

## RECTANGULAR SINGLE-GANG

- **Rugged, die-cast cover plate** with durable nickel or brass finish.
- **Scrub water compliant without caulking**, supplied with foam gasket and O-ring-equipped plugs.
- **Meet UL514C 2007 rev and NEC314.27c requirements** including scrub water for tile floors.

- **Includes receptacle, multimedia divider, Cat 5e jack, and F-connector.**



- **Large box flange** rests on finished floor — no adjustments needed.

FB1SRKS1

- **Swing-bracket mounting**, great for tile floors — eliminates drilling for mounting screws.



## ROUND SINGLE-GANG

- **Rugged, die-cast cover plate** with aluminum or brass finish.
- **Smooth, nearly flush appearance** when installed.
- **P&S 3232 or 885 duplex receptacles** included.
- **Multimedia divider** provided in low-voltage models.

- **Snap-in jack holder accommodates two snap-in multimedia jacks** for easy configuration. Choose from wide variety of P&S multimedia jacks for any application.

- **Hinged covers or threaded plugs.**



- **Extra-deep design** leaves plenty of wiring room.
- **Built-in ground terminal** makes ground bonding easy when required by code.

PS863PCOMAL

Catalog Number	Plate Finish	Description	Devices included
<b>Rectangular Single-Gang — wood sub-floors only</b>			
FB1SR_	Brass Nickel	Single Receptacle, Threaded Plug	15A Receptacle
FB1SRKS1_	Brass Nickel	Dual-Voltage, #8 Duplex Opening, Threaded Plugs	15A Receptacle, Cat 5e Jack, F-Connector, and Blanks
FB1DR_	Brass Nickel	#8 Duplex Opening, Threaded Plugs	3232 Receptacle
FB1KS4_	Brass Nickel	Low-Voltage #8 Duplex Opening, Threaded Plugs	Cat 5e Jack, F-Connector, and Blanks
<b>Rectangular Steel Single-Gang — wood sub-floors only</b>			
1542FBA	Brass	Steel Box With Single Threaded Plug	Single Receptacle
<b>Rectangular Two-Gang — wood sub-floors only</b>			
FB2DRKS4_	Brass Nickel	Two #8 Openings, Threaded Plugs	3232 Receptacle, Cat 5e Jack, F-Connector, and Blanks
FB2DR2_	Brass Nickel	Two #8 Openings, Threaded Plugs	Two 3232 Receptacles
FB2KS8_	Brass Nickel	Two Low-Voltage #8 Openings, Threaded Plugs	Cat 5e Jack, F-Connector, and Blanks

### NOTES

"B" suffix in FB Series catalog number denotes brass cover finish. Substitute "N" to denote nickel finish.  
PS862 Series covers available in hardwood, tile, and carpet models with brass or aluminum finish.

**For complete ordering details, ask your P&S representative or distributor.**



Catalog Number	Plate Finish	Description	Devices included
<b>Round — wood sub-floors only</b>			
TM1542-BOX	—	38" Cu. In. Plastic Box for use with TM1542 Covers	—
TM1542-XXX	White, Brown, Gray, Black, Light Almond, Paintable Gray	Non-Metallic Cover for use with TM1542-BOX	885 Decorator Receptacle
TM1542-FM	Brass	Low-Profile (1/4") Cover	885 Decorator Receptacle
<b>Round — wood or concrete sub-floors</b>			
PS862D_	Brass Aluminum	#8 Duplex Opening, Hinged Covers	3232 Receptacle
PS862TGFCI_	Brass Aluminum	#26 Decorator Opening, Hinged Covers	885 Decorator Receptacle
PS862TSP_	Brass Aluminum	#8 Duplex Opening, Screw Plugs	3232 Receptacle
PS862TCK12_	Brass Aluminum	Cover Conversion Kit 1-1/4" to 1/2" Screw Plug	—
PS862DPCOMAL	—	#8 Duplex Opening and Two Low-Voltage Openings, Hinged Covers	3232 Receptacle, Cat 5e Jack, F-Connector
<b>Round Components and Kits</b>			
PS862KIT	—	Concrete Kit	Mud Cap, Gasket, Two 3/4" Male PVC Conduit Fittings
PS862	—	Box only, covers available separately	Covers available separately

# P&S Floor Boxes – the easiest way to put receptacles and multimedia connections everywhere they're needed.

If you've installed P&S Wall, Ceiling, or Fan boxes, you know just what to expect in the P&S Floor Box Line: everything you're looking for. These affordable, high-value solutions bring you convenient access, rugged construction, and support for both line-voltage and low-voltage connections — which are easy to configure and install, because P&S offers a broad selection of wiring devices and multimedia jacks. P&S Floor Boxes install in wood and concrete floors and provide compatibility with a wide range of floor surfaces, including ceramic tile.

With P&S, you can take advantage of all the right choices in round and rectangular styles to accommodate either single- or two-gang applications. There's even a single-gang dual-voltage model — a P&S exclusive!



# Learn about all the P&S Floor Box choices.

Additional P&S Floor Box models, accessories, and finish options are available. For complete details, ask your P&S representative or distributor — or visit [www.passandseymour.com](http://www.passandseymour.com).

For additional technical or application-specific information, call 800-223-4185 or visit our website at [www.legrand.us/passandseymour](http://www.legrand.us/passandseymour). We're eager to put our expertise to work for you.

## **Legrand/Pass & Seymour**

P.O. Box 4822  
Syracuse, NY 13221-4822  
800-776-4035  
[www.legrand.us/passandseymour](http://www.legrand.us/passandseymour)

### **Distributed by:**



#### **North America Headquarters**

60 Woodlawn Street  
West Hartford, CT 06110  
Phone: 1.877.BY.LEGRAND (295.3472)  
Fax: 1.860.232.2062  
[www.legrand.us](http://www.legrand.us)

#### **Legrand Canada**

570 Applewood Crescent  
Vaughan, ON, L4K 4B4  
Phone: 905.738.9195  
Fax: 905.738.9721  
[www.legrand.ca](http://www.legrand.ca)