

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301410038](#)  
**Status:** **Active**  
**Overview:** [Heavy-Duty Industrial Wiring Devices](#)  
**Description:** Super-Safeway Connector, 2 Pole/3 Wire, NEMA 6-15, 250V

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA      LR6837  
 UL      E10176

**General**

Product Family      Wiring Devices  
 Series      [130141](#)  
 IP Rating      N/A  
 NEMA Configuration      NEMA 6-15  
 Overview      [Heavy-Duty Industrial Wiring Devices](#)  
 Product Literature Order No      987650-8068  
 Product Name      Super-Safeway  
 Receptacle Type      Single  
 Specialty      N/A  
 Type      Connector  
 UPC      78678870303  
 Woodhead      Yes

**Physical**


Flange      No  
 Flip Lid      No  
 Gender      Female  
 Length      N/A  
 Locking Blade      No  
 Poles      2-pole/3-wire

**Electrical**

Cord Type      N/A  
 Current - Maximum per Contact      15.0A  
 GFCI      No  
 Lighted Connector      No  
 Voltage - Maximum      250V

**Material Info**

Engineering Number      1549



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

|                 |              |
|-----------------|--------------|
| China ROHS      | Not Reviewed |
| ELV             | Not Reviewed |
| RoHS Phthalates | Not Reviewed |

**China RoHS**

**Search Parts in this Series**

[130141 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [1301410038](#)  
**Status:** **Active**  
**Overview:** [Heavy-Duty Industrial Wiring Devices](#)  
**Description:** Super-Safeway Connector, 2 Pole/3 Wire, NEMA 6-15, 250V

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

**Agency Certification**

CSA LR6837  
UL E10176

**General**

Product Family [Wiring Devices](#)  
Series [130141](#)  
IP Rating N/A  
NEMA Configuration NEMA 6-15  
Overview [Heavy-Duty Industrial Wiring Devices](#)  
Product Literature Order No 987650-8068  
Product Name Super-Safeway  
Receptacle Type Single  
Specialty N/A  
Type Connector  
UPC 78678870303  
Woodhead Yes

**Physical**


Flange No  
Flip Lid No  
Gender Female  
Length N/A  
Locking Blade No  
Poles 2-pole/3-wire

**Electrical**

Cord Type N/A  
Current - Maximum per Contact 15.0A  
GFCI No  
Lighted Connector No  
Voltage - Maximum 250V

**Material Info**

Engineering Number 1549



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**China RoHS**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

|                 |              |
|-----------------|--------------|
| China ROHS      | Not Reviewed |
| ELV             | Not Reviewed |
| RoHS Phthalates | Not Reviewed |

**Search Parts in this Series**

[130141 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION