



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **1597TRWRI Radiant Self Test TR WR Gfci 15A 125V Iv** *Pass & Seymour/Legrand*

|                  |                                                                                                                                                                                                                                                                          |
|------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | 1597TRWRI                                                                                                                                                                                                                                                                |
| Manufacturer     | Pass & Seymour/Legrand                                                                                                                                                                                                                                                   |
| Description      | Self-Test Duplex Receptacle, 15 A, 125 V, 2 Poles, #14 to #10 Awg Compatible Wire Size, Control Circuit Actuator, Back and Side Wired Connection, 60 HZ, 1.73 In Width, 4.20 In Height, Thermoplastic Material, Ivory, 0.025 Sec Trip Time, Weather Resistant, 0.2800 LB |
| Weight per unit  | 0.2750 (lbs/each)                                                                                                                                                                                                                                                        |
| Product Category | Gen Purpose Recept & Surge Pro                                                                                                                                                                                                                                           |

### **Features**

|                  |                                                      |
|------------------|------------------------------------------------------|
| actuator         | Control Circuit                                      |
| amperage rating  | 15                                                   |
| connection       | Back and side wire                                   |
| indoor/outdoor   | Outdoor                                              |
| interrupt rating | 4 to 6 mA                                            |
| Mounting Type    | Box                                                  |
| Number of Gangs  | 1.0                                                  |
| Outlet Type      | Tamper-Resistant, Self-Test, Weather-Resistant, GFCI |
| Poles            | 2                                                    |
| trip range       | 4 to 6 mA                                            |
| Trip Type        | .025 Second Nominal                                  |
| Voltage Rating   | 125                                                  |

### **Dimensions and Weight**

|        |      |
|--------|------|
| Length | 1.03 |
| Width  | 1.73 |

### **Descriptions**

|                        |                                          |
|------------------------|------------------------------------------|
| Description            | RADIANT SELF TEST TR WR GFCI 15A 125V IV |
| extra long description | P&S 1597TRWRI RADIANT SELF TEST TR       |

### **Manufacturer Information**

|       |                |
|-------|----------------|
| Brand | Pass & Seymour |
| GTIN  | 00785007036138 |
| UPC   | 785007036138   |

### **Taxonomies, Classifications, and Categories**

|                      |                                                                 |
|----------------------|-----------------------------------------------------------------|
| Category Description | Residential GFCI devices                                        |
| Type                 | Specification Grade Weather-Resistant 15A Self-Test Duplex GFCI |

### **Trade Size**

|          |      |
|----------|------|
| Amperage | 15.0 |
|----------|------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

|                 |       |
|-----------------|-------|
| Carton          | 1     |
| Package         | 10    |
| Weight Per each | 0.275 |

## Uses, Certifications, and Standards

|                          |                                   |
|--------------------------|-----------------------------------|
| environmental conditions | 95% Humidity, UL 94 V2            |
| Operating Temperature    | -35°C to +66°C                    |
| standard                 | CULUS, UL, cULus, UL Listed, FSUL |