



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **161464XSCHC Encl 16X14X6 N4X CH Clamp CVR**

*Cooper B-Line/Cable Tray*

|                  |                                                                                                                                                                                                                                 |
|------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | 161464XSCHC                                                                                                                                                                                                                     |
| Manufacturer     | Cooper B-Line/Cable Tray                                                                                                                                                                                                        |
| Description      | Eaton B-Line Series Jic Panel Enclosure, 16" Height, 6" Length, 14" Width, Nema 4X, Hinged Cover, 4XSCHC Enclosure, Wall Mount, Small Single Door, External Mounting Feet, 304 Stainless Steel, Seamless Poured In-Place Gasket |
| Weight per unit  | 15.7 (lbs/each)                                                                                                                                                                                                                 |
| Product Category | Nema Types 4 & 4X Metallic Enc                                                                                                                                                                                                  |

### **Features**

|            |                                     |
|------------|-------------------------------------|
| dimensions | 6.0000 IN X 14.0000 IN X 16.0000 IN |
| Material   | Stainless Steel                     |

### **Material, Color, and Finish**

|       |      |
|-------|------|
| Color | Gray |
|-------|------|

### **Dimensions and Weight**

|       |       |
|-------|-------|
| Depth | 6.00  |
| Width | 14.00 |

### **Descriptions**

|                        |                                                                                                                                                                                                                                         |
|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description            | ENCL 16X14X6 N4X CH CLAMP CVR                                                                                                                                                                                                           |
| extra long description | B-LINE 16146-4XSCHC TYPE 4X SSL JIC                                                                                                                                                                                                     |
| Features               | Eaton's B-Line series JIC panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments, but are also commonly used as industrial wiring, junction, pull, and termination boxes. |
| Long Description       | Eaton B-Line series JIC panel enclosure, 16" height, 6" length, 14" width, NEMA 4X, Hinged cover, 4XSCHC enclosure, Wall mount, Small single door, External mounting feet, 304 stainless steel, Seamless poured in-place gasket         |
| Product Type           | Type 4X SSL Jic Continuous Hinge CVR Enc, 16X14X6                                                                                                                                                                                       |
| Special Features       | Cont. piano hinge,panel mount prov.,s.s.doorclamps                                                                                                                                                                                      |

### **Manufacturer Information**

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00782051702729 |
| Manufacturers Part Number | 16146-4XSCHC   |
| UPC                       | 782051702729   |

### **Taxonomies, Classifications, and Categories**

|                      |                      |
|----------------------|----------------------|
| Category Description | STEEL JUNCTION BOXES |
| Type                 | JIC panel enclosure  |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

|                 |        |
|-----------------|--------|
| Carton          | 1      |
| Weight Per each | 15.746 |

## Uses, Certifications, and Standards

|             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
|-------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Application | Ind Facilities & Factories - Facility: Power Distribution and Control<br>Ind Facilities & Factories - Mfg. Process Electrification and Control<br>Commercial / Institutional Buildings / Structures - Critical Power<br>Ind Facilities & Factories - Facility: Safety and Security Systems<br>Ind Facilities & Factories - Industrial Facilities/Factories - Other<br>Commercial / Institutional Buildings / Structures - Power Distribution and Controls<br>Commercial / Institutional Buildings / Structures - Lighting and Lighting Controls<br>Ind Faci |
| Mounting    | WALL                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| standard    | NEMA, CSA C22.2., UL 50                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |