

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301460060](#)  
**Status:** **Active**  
**Overview:** [Watertite Wet-Location Wiring Solutions](#)  
**Description:** Watertite Connector, 2 Pole/3 Wire, NEMA 5-15, 125V, Cord Grip Body Size F2

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA	LR6837
UL	E10176

**General**

Product Family	Wiring Devices
Series	<a href="#">130146</a>
Exclude SD Check	Yes
IP Rating	IP67
NEMA Configuration	NEMA 5-15
Overview	<a href="#">Watertite Wet-Location Wiring Solutions</a>
Product Literature Order No	987650-8067
Product Name	Watertite
Receptacle Type	Single
Specialty	N/A
Type	Connector
UPC	78678871102

**Physical**

Cord Grip Body Size	F2 1/2"
Flange	No
Flip Lid	No
Gender	Female
Length	N/A
Locking Blade	No
Net Weight	186.426/g
Poles	2-pole/3-wire

**Electrical**

Cord Type	N/A
Current - Maximum per Contact	15.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	125V

**Material Info**

Engineering Number	15W47
--------------------	-------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130146 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301460060](#)  
**Status:** **Active**  
**Overview:** [Watertite Wet-Location Wiring Solutions](#)  
**Description:** Watertite Connector, 2 Pole/3 Wire, NEMA 5-15, 125V, Cord Grip Body Size F2

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA      LR6837  
UL      E10176

**General**

Product Family      Wiring Devices  
Series      [130146](#)  
Exclude SD Check      Yes  
IP Rating      IP67  
NEMA Configuration      NEMA 5-15  
Overview      [Watertite Wet-Location Wiring Solutions](#)  
Product Literature Order No      987650-8067  
Product Name      Watertite  
Receptacle Type      Single  
Specialty      N/A  
Type      Connector  
UPC      78678871102

**Physical**

Cord Grip Body Size      F2 1/2"  
Flange      No  
Flip Lid      No  
Gender      Female  
Length      N/A  
Locking Blade      No  
Net Weight      186.426g  
Poles      2-pole/3-wire

**Electrical**

Cord Type      N/A  
Current - Maximum per Contact      15.0A  
GFCI      No  
Lighted Connector      No  
Voltage - Maximum      125V

**Material Info**

Engineering Number      15W47



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

**China RoHS**

**Search Parts in this Series**

[130146 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**