



Standard size wallplates duplex receptacle

Product description


1-Gang, 2-Gang, 3-Gang



1-Gang



2-Gang



3-Gang

Duplex receptacle


Gang	Material	Color suffix	Catalog no.		
1-Gang	Nylon	A, B, BK, GY, LA, RD, V, W	□ 5132__	•	•
	Thermoset	A, B, LA, V, W	□ 2132__	•	•
	302/304 stainless steel	—	□ 93101	•	•
	CuVerro® antimicrobial copper	CU, CUR	□ 93101__	•	•
	Brass	—	□ 94101	•	•
2-Gang	Nylon	A, B, BK, GY, LA, RD, V, W	□ 5150__	•	•
	Thermoset	A, B, LA, V, W	□ 2150__	•	•
	302/304 stainless steel	—	□ 93102	•	•
	CuVerro® antimicrobial copper	CU, CUR	□ 93102__	•	•
	Brass	—	□ 94102	•	•
3-Gang	302/304 stainless steel	—	□ 93103	•	•
	CuVerro® antimicrobial copper	CU, CUR	□ 93103__	•	•

See additional CuVerro® wallplate information on K-22

Standard size wallplates single receptacle

Product description

1-Gang



1-Gang


Single receptacle

Gang	Material	Color suffix	Catalog no.		
1-Gang with 1.406" (35.712mm) hole	Nylon	A, B, BK, GY, RD, V, W	□ 5131__	•	•
	Thermoset	A, B, LA, V, W	□ 2131__	•	•
	302/304 stainless steel	—	□ 93091	•	•
	CuVerro® antimicrobial copper	CU, CUR	□ 93091__	•	•
	Brass	—	□ 94091	•	•

See additional CuVerro® wallplate information on K-22

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), RD (Red), V (Ivory), W (White), CU (White Bronze) CuVerro® ONLY, CUR (Rose) CuVerro® ONLY



Certification information: 2000, 4000, 5000, ST & PJ series wallplates are cULus Listed; 93000 series wallplates are UL Listed and CSA Certified; 94000 series are UL Listed and CSA certified; CuVerro® series wallplates are only UL Listed. **Specification information:** K-22

Compliances, specifications and availability are subject to change without notice.


Indicates NAFTA compliant - Page Q-30

RoHS compliant - Page Q-30


Standard size wallplates duplex receptacle

Product description


1-Gang, 2-Gang, 3-Gang



1-Gang





2-Gang



3-Gang

Duplex receptacle


Gang	Material	Color suffix	Catalog no.	 
1-Gang	Nylon	A, B, BK, GY, LA, RD, V, W	□ 5132__	• •
	Thermoset	A, B, LA, V, W	□ 2132__	• •
	302/304 stainless steel	—	□ 93101	• •
	CuVerro® antimicrobial copper	CU, CUR	□ 93101__	• •
	Brass	—	□ 94101	• •
2-Gang	Nylon	A, B, BK, GY, LA, RD, V, W	□ 5150__	• •
	Thermoset	A, B, LA, V, W	□ 2150__	• •
	302/304 stainless steel	—	□ 93102	• •
	CuVerro® antimicrobial copper	CU, CUR	□ 93102__	• •
	Brass	—	□ 94102	• •
3-Gang	302/304 stainless steel	—	□ 93103	• •
	CuVerro® antimicrobial copper	CU, CUR	□ 93103__	• •

See additional CuVerro® wallplate information on K-22

Standard size wallplates single receptacle



Product description

1-Gang



1-Gang


Single receptacle

Gang	Material	Color suffix	Catalog no.	 
1-Gang with 1.406" (35.712mm) hole	Nylon	A, B, BK, GY, RD, V, W	□ 5131__	• •
	Thermoset	A, B, LA, V, W	□ 2131__	• •
	302/304 stainless steel	—	□ 93091	• •
	CuVerro® antimicrobial copper	CU, CUR	□ 93091__	• •
	Brass	—	□ 94091	• •

See additional CuVerro® wallplate information on K-22

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), RD (Red), V (Ivory), W (White), CU (White Bronze) CuVerro® ONLY, CUR (Rose) CuVerro® ONLY



Certification information: 2000, 4000, 5000, ST & PJ series wallplates are cULus Listed; 93000 series wallplates are UL Listed and CSA Certified; 94000 series are UL Listed and CSA certified; CuVerro® series wallplates are only UL Listed. **Specification information:** K-22

Compliances, specifications and availability are subject to change without notice.

 Indicates NAFTA compliant - Page Q-30

 RoHS compliant - Page Q-30