

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301420038](#)  
**Status:** **Active**  
**Overview:** [Heavy-Duty Industrial Wiring Devices](#)  
**Description:** Super-Safeway Plug with Locking Blade, 3 Pole/4 Wire, NEMA L16-30, 3ø 480V

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

**Agency Certification**

CSA LR6837  
 UL E10176

**General**

Product Family [Wiring Devices](#)  
 Series [130142](#)  
 IP Rating N/A  
 NEMA Configuration NEMA L16-30  
 Overview [Heavy-Duty Industrial Wiring Devices](#)  
 Product Literature Order No 987650-8068  
 Product Name Super-Safeway  
 Receptacle Type N/A  
 Specialty N/A  
 Type Plug  
 UPC 78678870434  
 Woodhead Yes

**Physical**

Flange No  
 Flip Lid No  
 Gender Male  
 Length N/A  
 Locking Blade Yes  
 Poles 3-pole/4-wire

**Electrical**

Cord Type N/A  
 Current - Maximum per Contact 30.0A  
 GFCI No  
 Lighted Connector No  
 Voltage - Maximum 3Ø 480V

**Material Info**

Engineering Number 2876



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Not Reviewed

ELV Not Reviewed

RoHS Phthalates Not Reviewed

**Search Parts in this Series**

[130142 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301420038](#)  
**Status:** **Active**  
**Overview:** [Heavy-Duty Industrial Wiring Devices](#)  
**Description:** Super-Safeway Plug with Locking Blade, 3 Pole/4 Wire, NEMA L16-30, 3ø 480V

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA      LR6837  
 UL      E10176

**General**

Product Family      Wiring Devices  
 Series      [130142](#)  
 IP Rating      N/A  
 NEMA Configuration      NEMA L16-30  
 Overview      [Heavy-Duty Industrial Wiring Devices](#)  
 Product Literature Order No      987650-8068  
 Product Name      Super-Safeway  
 Receptacle Type      N/A  
 Specialty      N/A  
 Type      Plug  
 UPC      78678870434  
 Woodhead      Yes

**Physical**

Flange      No  
 Flip Lid      No  
 Gender      Male  
 Length      N/A  
 Locking Blade      Yes  
 Poles      3-pole/4-wire

**Electrical**

Cord Type      N/A  
 Current - Maximum per Contact      30.0A  
 GFCI      No  
 Lighted Connector      No  
 Voltage - Maximum      3Ø 480V

**Material Info**

Engineering Number      2876



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

**China RoHS**

**Search Parts in this Series**

[130142 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**