



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2BLT440LADPLP840 2X4 Led BSKT Trof 40K 4000LM

Lithonia Lighting - Acuity

Catalog Number	2BLT440LADPLP840
Manufacturer	Lithonia Lighting - Acuity
Description	The 2 FT. X 4 FT. BLT Low-Profile Recessed Led Lay-In By Lithonia Lighting Is What You've Come to Expect From The Leader In Lighting. With Its Endless Options and Configurations, BLT Provides The Versatility You Need At A Value That Can'T Be Beat. With A Curved, Linear Center Element, The BLT Provides A Consistent Look and Performance Throughout The Entire Application and Replaces Fluorescent Fixtures to Optimize Led Savings.
Weight per unit	17.8 (lbs/each)
Product Category	Led Recessed Architectural & S

Features

average life	60,000
dimmable	Yes
Hardware	No
Lamp Included	Yes
Lamp Type	LED - Static
lumens	4000 LM
Material	Steel
Maximum Operating Temperature	25
pallet quantity	26
Power Source	Hardwired
Shape	Rectangular
Voltage Rating	120-277
Warranty	5
Wattage	31.7

Material, Color, and Finish

Color	White
color rendering index (cri)	80
color temperature	4000
Finish	Matte
Lens Color	WHITE
Lens Material	Acrylic
Style	Traditional



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Dimensions and Weight

Height	3.5
Length	50
Width	25

Descriptions

Construction	New Construction,Remodel
Description	2X4 LED BSKT TROF 40K 4000LM
extra long description	LITH 2BLT4 40L ADP LP840 Basket LED
Features	Design Select
Long Description	The 2 ft. x 4 ft. BLT low-profile recessed LED lay-in by Lithonia Lighting is what you've come to expect from the leader in lighting. With its endless options and configurations, BLT provides the versatility you need at a value that can't be beat. With a curved, linear center element, the BLT provides a consistent look and performance throughout the entire application and replaces fluorescent fixtures to optimize LED savings.
Product Type	Troffer
Special Features	The BLT Best-in-Value Low Profile LED luminaire features a popular center basket design that offers a clean, versatile style and volumetric distribution. High efficacy LED light engines deliver energy savings and low maintenance compared to traditional sources. An extensive selection of configurations and options make the BLT the perfect choice for many lighting applications including schools, offices and other commercial spaces, retail, hospitals and healthcare facilities. The low profile BLT design (2-3/

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00190887470765
Manufacturers Part Number	2BLT4 40L ADP LP840
UPC	190887470765

Taxonomies, Classifications, and Categories

Category Description	Led Lighting
Type	Troffer

Trade Size

aperture size	2x4
---------------	-----

Packaging

Carton	1
Weight	14.148
Weight Per each	17.75



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Ambulatory Care
environmental conditions	Indoor
Mounting	Recessed
standard	CSA