



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 301163 Weatherproof Wire Conn, 63 Gray/DK Blue, 15/Card

*Ideal*

Catalog Number	301163
Manufacturer	Ideal
Description	MDL 63 Gray-Blue 15 Clam
Weight per unit	0.0010 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### Features

Quantity	Card of 15
----------	------------

### Material, Color, and Finish

Color	Gray
-------	------

### Descriptions

Description	WEATHERPROOF WIRE CONN, 63 GRAY/DK BLUE, 15/CARD
extra long description	IDEAL 30-1163 MDL 63 GRAY-BLUE 15 C
Features	100% Silicone-based sealant protects against moisture and corrosionUL Listed to 486G Sealed Twist-On Wire Connector for use in damp/wet locations or above-grade applicationsEasy to apply, pre-filled twist-on wire connectorsSwept wing design is built for comfort and efficiencyEliminates the need for heat-shrink or excessive tapingTough, UL 94V-2 flame-retardant shell rated at 105°C (221°F)Models 61 and 63 approved for bonding and grounding applicationsFor use in damp/wet location or above-grade applications
Long Description	MDL 63 GRAY-BLUE 15 CLAM
Product Type	MDL 63 Gray-Blue 15 Clam
Special Features	Silicone-based sealant protects against moisture and corrosion. Easy to apply pre-filled twist-on wire connectors

### Manufacturer Information

Brand	Ideal
GTIN	00783250758166
Manufacturers Part Number	30-1163
UPC	783250758166

### Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Model 63® Connector

### Availability

minimum qty	15
-------------	----



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	15
Package	75
Weight Per each	0.001

## Uses, Certifications, and Standards

Application	Handles wire sizes from #16 to #6 AWG copper. Minimum of 3 #14 AWG. Maximum of 2 #8 & 1 #10 AWG.
standard	UL listed for 486D for use in damp/wet locations