



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 30171 Wire-Nut Wire Conn, Model 71B Gray, 1, 000/Box

*Ideal*

|                  |   |
|------------------|---|
| Catalog Number   | 30171   |
| Manufacturer     | Ideal   |
| Description      | Ideal, Wire Connector, Wire-Nut, Twist-On, Number Of Conductors: 1 to 5, Conductor Range: 22 - 16 Awg, Min 2-16AWG Max 2-16AWG, Color: Gray, Material: Flame-Retardant Polypropelene, Voltage Rating: 300 V, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Model Number: 71B, Flammability Rating: UI 94V-2 |
| Weight per unit  | 0.0010 (lbs/each)   |
| Product Category | Electrical Fixture Conn ( Nuts  |

### Features

|                |                               |
|----------------|-------------------------------|
| Material       | Flame-retardant Polypropelene |
| Voltage Rating | 300                           |

### Material, Color, and Finish

|       |      |
|-------|------|
| Color | Gray |
|-------|------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | WIRE-NUT WIRE CONN, MODEL 71B GRAY, 1,000/BOX  |
| extra long description | IDEAL 30-171 WIRENUT 71B GRAY, 1000  |
| Features               | The IDEAL Wire-Nut Wire Connector set new standards for innovation, quality and convenience when it was first introduced in 1928. As the first screw-on wire connector in America, it literally set the industry standard for years to come. With a fixed, square-wire spring and a positive grip shell, the Wire-Nut is perfect to twist-on with fingers for a secure connection that will last. The refined wire range makes it the best choice for fine stranded wire applications. The Wire-Nut also features a tough, flame     |
| Long Description       | IDEAL, Wire Connector, Wire-Nut, Twist-On, Number Of Conductors: 1 to 5, Conductor Range: 22 - 16 AWG, Min 2-16AWG MAX 2-16AWG, Color: Gray, Material: Flame-retardant polypropelene, Voltage Rating: 300 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Model Number: 71B, Flammability Rating: UL 94V-2  |
| Product Type           | Wirenut 71B Gray, 1000 Carton  |
| Special Features       | Comply With Federal Specification W-S-610E; Deep Skirt Helps Protect Against Flash-Over; Features: Fixed, Square-Wire Spring Creates Its Own Threads Maintains A Secure Positive Grip That Will Not Relax Over Time; Flammability Rating: UL 94V-2; Model Number: 71B; No Pre-Twisting Required Positive Grip Design Provides Fast, Easy Installation; Reusable For Easy Circuit Changes And Additions; Tough, UL94V-2 Flame-Retardant Shell Rated At 105 Degree C (221 Degree F); UL Listed To 486C And CSA Certified To C22.2 #188 |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Ideal          |
| GTIN                      | 00783250301713 |
| Manufacturers Part Number | 30-171         |
| UPC                       | 783250301713   |

## Taxonomies, Classifications, and Categories

|                      |           |
|----------------------|-----------|
| Category Description | WIRE NUTS |
| Type                 | Twist-On  |

## Availability

|             |      |
|-------------|------|
| minimum qty | 1000 |
|-------------|------|

## Packaging

|                 |       |
|-----------------|-------|
| Carton          | 1000  |
| Weight Per each | 0.001 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

|                          |  |
|--------------------------|--|
| Application              | Insulating or Joining 2 or more conductors   |
| environmental conditions | Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)                             |
| standard                 | CSA Certified to C22.2 #188, UL Listed to 486C, complies with Federal Specification W-S-610E |