



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 31012 Thumb Winder Fish Tape, 25' X 1/8", X .045"

*Ideal*

|                  |  |
|------------------|--|
| Catalog Number   | 31012  |
| Manufacturer     | Ideal  |
| Description      | Ideal, Fish Tape, Blued-Steel, Thumb -Winder, Length: 25 FT, Width: 1/8 In, Thickness: 045 In, Tensile Strength: 1600 LB, Tape End: Formed Hook, Material: Highest Grade Carbon Steel, Case Diameter: 7 In |
| Weight per unit  | 0.9200 (lbs/each)  |
| Product Category | Fishing Equipment  |

### Features

|                  |                            |
|------------------|----------------------------|
| Material         | Highest Grade Carbon Steel |
| tape end         | Formed Hook                |
| Tensile Strength | 1600                       |

### Dimensions and Weight

|           |     |
|-----------|-----|
| Length    | 25  |
| Thickness | 045 |
| Width     | 1/8 |

### Descriptions

|                        |  |
|------------------------|--|
| Description            | THUMB WINDER FISH TAPE, 25' X 1/8", X .045"  |
| extra long description | IDEAL 31-012 Fish Tape,IDEAL,Blued-  |
| Features               | Perfect for longer conduit runs, this fish tape boasts the highest tensile strength, and highest grade carbon steel for professional durability and reliability. The Blued-Steel also provides rust and corrosion resistance for longer life.      |
| Long Description       | IDEAL, Fish Tape, Blued-Steel, Thumb -Winder, Length: 25 FT, Width: 1/8 IN, Thickness: 045 IN, Tensile Strength: 1600 LB, Tape End: Formed Hook, Material: Highest Grade Carbon Steel, Case Diameter: 7 IN   |
| Product Type           | Fish Tape, Ideal, Blued-Steel, Thumb -Winder, 25.000 FT Len, 1/8   |
| Special Features       | Features: Unique Finish Is Non-Oily And Resists Rust; Industry's Straightest Wire; Stiffer For Long Runs; Highest Grade Carbon Steel; Tensile Strength 1,600 LB; Multiple Options In Width, Length And Eyelet For Ease Of Use; Case Diameter: 7 IN |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Ideal          |
| GTIN                      | 00783250310128 |
| Manufacturers Part Number | 31-012         |
| UPC                       | 783250310128   |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... HAND TOOLS .....

## Packaging

Carton ..... 1 .....

Weight Per each ..... 0.92 .....