



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 324 1-1/4" Plastic Bushing

*Bridgeport Fittings*

|                  |   |
|------------------|---|
| Catalog Number   | 324   |
| Manufacturer     | Bridgeport Fittings   |
| Description      | Plastic Bushing, 1-1/4 In Trade Size, Gray, Insulated, Straight Connection Orientation, Rigid Connection, 1-15/16 In Width, 1/2 In Height, 1-15/16 In Diameter, +150 °C Operating Temperature, 0.0167 LB/Ea |
| Weight per unit  | 0.0167 (lbs/each)   |
| Product Category | Plastic   |

### Features

|          |         |
|----------|---------|
| Material | Plastic |
| media    | Yes     |

### Material, Color, and Finish

|        |           |
|--------|-----------|
| Color  | Gray      |
| Finish | NO FINISH |

### Dimensions and Weight

|      |       |
|------|-------|
| Size | 1-1/4 |
|------|-------|

### Descriptions

|                        |                                |
|------------------------|--------------------------------|
| Description            | 1-1/4" PLASTIC BUSHING         |
| extra long description | BPT 324 1-1/4" PLASTIC BUSHING |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | Bridgeport     |
| GTIN  | 00781747003249 |
| UPC   | 781747003249   |

### Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | COUPLINGS, ADAPTERS, REDUCERS, BUSHINGS, & CAPS |
| Type                 | BUSHING   |

### Trade Size

|            |      |
|------------|------|
| Trade Size | 1.25 |
|------------|------|

### Packaging

|                 |        |
|-----------------|--------|
| Carton          | 100    |
| Weight Per each | 0.0167 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Used with locknut to terminate threaded rigid and IMC to box, or used with connector to prevent damage to wire insulation. Rated 105 degree C.

standard

UL

Temperature Rating

105°C