



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



35194 Phillip Screwdriver 1/4 X 4" X #2

Ideal

| | |
|------------------|---|
| Catalog Number | 35194 |
| Manufacturer | Ideal |
| Description | Ideal, Screwdriver, Phillips, Phillips Head Screws, Tip Size: #2, Overall Length: 8-3/8 In, Shank Length: 4 In, Handle Type: Cushioned Rubber Grip, Blade Material: Chrome Vanadium Steel, Blade Finish: Nickel-Chrome Plating, Tip Type: Phillips, Shank Size: #2 In, Warranty: Lifetime Guarantee |
| Weight per unit | 0.2833 (lbs/each) |
| Product Category | Pliers, Wrenches, Saw, Pouches |

Features

| | |
|--------------|-----------------------|
| Handle Type | Cushioned Rubber Grip |
| Shank Length | 4 |
| Tip Size | #2 |
| tip type | Phillips |

Material, Color, and Finish

| | |
|----------------|-----------------------|
| Blade Material | Chrome Vanadium Steel |
|----------------|-----------------------|

Dimensions and Weight

| | |
|----------------|-------|
| Overall Length | 8-3/8 |
|----------------|-------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | PHILLIP SCREWDRIVER 1/4 X 4" X #2 |
| extra long description | IDEAL 35-194 Screwdriver, Ideal, PHL, |
| Features | The Phillips Cushioned-Grip Screwdrivers boast a rugged, nickel-chrome plating, great for corrosion resistance. These screwdrivers offer several different tip sizes and feature FastFinder handles that quickly help the user identify the tip type on the end of the handle. The cushion-grip handles are resistant to oil, gas and water, helping to prevent slippage for greater torque and superior comfort. For easy identification, the handle ends are color-coded. |
| Long Description | IDEAL, Screwdriver, Phillips, Phillips Head Screws, Tip Size: #2, Overall Length: 8-3/8 IN, Shank Length: 4 IN, Handle Type: Cushioned Rubber Grip, Blade Material: Chrome Vanadium Steel, Blade Finish: Nickel-Chrome Plating, Tip Type: Phillips, Shank Size: #2 IN, Warranty: Lifetime Guarantee |
| Product Type | Screwdriver, Ideal, PHL, PHL Head Screws, #2 Tip, 8-3/8 In Overall |
| Special Features | Features: Vapor-Blasted Tip Prevents Plate Chipping; Nickel-Chrome Plating For Corrosion Resistance; Tough, Chrome Vanadium Steel Shank; Cushioned Rubber Grip; Lifetime Guarantee; Identification Mark On Ends; Shank Size: #2 IN; Warranty: Lifetime Guarantee |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250351947 |
| Manufacturers Part Number | 35194 |
| UPC | 783250351947 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------------|
| Category Description | HAND TOOLS |
| Type | Phillips, Phillips Head Screws |

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Weight Per each | 0.2833 |