



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



35203 Number 2 Phillips Speed Driver

Ideal

| | |
|------------------|---------------------------------------|
| Catalog Number | 35203 |
| Manufacturer | Ideal |
| Description | Ideal 35-203 Screwdriver, Ideal, Quic |
| Weight per unit | 0.3500 (lbs/each) |
| Product Category | Pliers, Wrenches, Saw, Pouches |

Features

| | |
|--------------|-----------------------|
| Handle Type | Cushioned Rubber Grip |
| Shank Length | 6 |
| Tip Size | 3/16 |
| tip type | Phillips |

Material, Color, and Finish

| | |
|----------------|-----------------------|
| Blade Material | Chrome Vanadium Steel |
|----------------|-----------------------|

Dimensions and Weight

| | |
|----------------|-------|
| Overall Length | 9-3/4 |
|----------------|-------|

Descriptions

| | |
|-------------|--------------------------------|
| Description | NUMBER 2 PHILLIPS SPEED DRIVER |
|-------------|--------------------------------|

Features
The Cabinet Quick Rotating Screwdriver is ideal for threading screws in switches, fixtures and anchors. For quick and easy use, it provides one-handed crank action. It has shank diameter that matches blade tip for tough applications and features a cross-ground tip to provide a precise and secure fit in the screw slot. Plate chipping is prevented by a vapor-blasted tip, and the screwdriver's nickel-chrome plating offers corrosion resistance and a smooth feel. The Cabinet Quick Rotating Screwdriver also feat

| | |
|------------------|---------------------------------------|
| Long Description | IDEAL 35-203 Screwdriver, Ideal, Quic |
|------------------|---------------------------------------|

| | |
|--------------|--|
| Product Type | Screwdriver, Ideal, Quick-Rotating, PHL Head, 3/16 In Tip, 9-3/4 |
|--------------|--|

Special Features
Features: Ideal For Threading Screws In Switches, Fixtures And Anchors; One-Handed Crank Action For Quick And Easy Use; Vapor-Blasted Tip Prevents Plate Chipping; Cross-Ground Tip Provides Precise And Secure Fit In Screw Slot; Nickel-Chrome Plating For Corrosion Resistance; Tough, Chrome Vanadium Steel Shank; Cushioned Rubber Grip; Lifetime Guarantee; Identification Mark On Ends; Shank Size: 3/16 IN



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250352036 |
| Manufacturers Part Number | 35-203 |
| UPC | 783250352036 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------------|
| Category Description | HAND TOOLS |
| Type | Quick-Rotating, Phillips Head |

Availability

| | |
|---------------------|----------|
| Manufacturer Status | Inactive |
|---------------------|----------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.35 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | For Threading Screws In Switches, Fixtures And Anchors |
|-------------|--|