

No. 7 Corrosive chemical pipe thread sealant

Code	Description	Qty.
17432	1 pt.	4

- FEATURES**
- Soft Set
 - Lead free

Application • Slow drying sealant for use with lines carrying corrosive chemicals: diluted acids, caustics and other chemical solutions



- Recommended for**
- Galvanized Steel
 - Iron
 - Brass
 - Copper
 - Aluminum
 - Stainless Steel



No. 21 Black, slow dry/soft set pipe thread sealant

Code	Description	Qty.
28651	½ pt.	24
28541	1 pt.	12
28371	1 gal.	4
28111	5 gal.	1
28222	55 gal.	1



- FEATURES**
- Black sealant
 - Lead free
 - Multi-purpose



Application • Soft set sealant for lines carrying a wide range of liquids and gases • For applications where black color is preferred • Brushable from 20°F to 140°F

- Recommended for**
- Galvanized Steel
 - Iron
 - Brass
 - Copper
 - Aluminum
 - Stainless Steel
 - Polyethylene
 - RTRP
 - PVC

Also available in 55 gal. container.

PTFE Tape 100% pure PTFE pipe thread sealant tape

Code	Description	Qty.
35942	½" x 260"	12
35943	½" x 520"	12
35944	½" x 1296"	12
35945	¾" x 260"	12
35946	¾" x 520"	12
35947	¾" x 1296"	12
35948	1" x 260"	12
35949	1" x 520"	12



Application • Resistant to most liquids and gases as it is completely inert

- Available in a wide variety of sizes.



No. 7 Corrosive chemical pipe thread sealant

Code	Description	Qty.
17432	1 pt.	4

FEATURES

- Soft Set
- Lead free

Application • Slow drying sealant for use with lines carrying corrosive chemicals: diluted acids, caustics and other chemical solutions



- Recommended for**
- Galvanized Steel
 - Iron • Brass • Copper • Aluminum
 - Stainless Steel



No. 21 Black, slow dry/soft set pipe thread sealant

Code	Description	Qty.
28651	½ pt.	24
28541	1 pt.	12
28371	1 gal.	4
28111	5 gal.	1
28222	55 gal.	1



FEATURES

- Black sealant
- Lead free
- Multi-purpose



Application • Soft set sealant for lines carrying a wide range of liquids and gases • For applications where black color is preferred

- Brushable from 20°F to 140°F

- Recommended for**
- Galvanized Steel • Iron
 - Brass • Copper • Aluminum
 - Stainless Steel
 - Polyethylene
 - RTRP • PVC

Also available in 55 gal. container.

PTFE Tape 100% pure PTFE pipe thread sealant tape

Code	Description	Qty.
35942	½" x 260"	12
35943	½" x 520"	12
35944	½" x 1296"	12
35945	¾" x 260"	12
35946	¾" x 520"	12
35947	¾" x 1296"	12
35948	1" x 260"	12
35949	1" x 520"	12

Application • Resistant to most liquids and gases as it is completely inert

- Available in a wide variety of sizes.

