



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 35988 Ratch-A-Nut 9-In-1 Screwdriver

*Ideal*

|                  |  |
|------------------|--|
| Catalog Number   | 35988  |
| Manufacturer     | Ideal  |
| Description      | Ratch-A-Nut 9-In-1 Screwdriver, Textured, Ergonomic, Slip Resistant Comfort-Grip Handle, Santoprene Handle, Chrome Vanadium Blade, Includes: 1/4 In and 3/16 In Slotted, #1 and #2 Phillips, 1/4 In, 5/16 In, 7/16 In Nutdrivers, Ratcheting Screwdriver End, Ratcheting Wire Connector Wrench |
| Weight per unit  | 0.7000 (lbs/each)  |
| Product Category | Pliers, Wrenches, Saw, Pouches   |

### Features

|             |  |
|-------------|--|
| Handle Type | Textured, Ergonomic, Slip Resistant Comfort-Grip |
|-------------|--|

### Material, Color, and Finish

|                 |                 |
|-----------------|-----------------|
| Blade Material  | Chrome Vanadium |
| Handle Material | SANTOPRENE      |

### Descriptions

|                        |  |
|------------------------|--|
| Description            | RATCH-A-NUT 9-IN-1 SCREWDRIVER   |
| extra long description | IDEAL 35-988 Screwdriver, Ideal, Ratch   |
| Features               | Patented Wire Connector Wrench accepts a wide variety of connectors and reduces finger fatigue. Pro-quality, 28 tooth, all metal ratchet can handle 225 lbs. of torque without failure. Ergonomic, slip-free textured grip provides excellent torque and is impervious to perspiration, gas, oil and chemicals. Accepts Twist-a-Nut replacement bits. Bits included: 1/4 in. Slotted, 3/16 in. Slotted, #1 Phillips, #2 Phillips, 1/4 in. Nutdriver, 5/16 in. Nutdriver, and 7/16 in. Nutdriver. Ratch-a-Nut 9-in-1 Screwdriver includes |
| Long Description       | Ratch-a-Nut 9-In-1 Screwdriver, Textured, Ergonomic, Slip Resistant Comfort-Grip Handle, Santoprene Handle, Chrome Vanadium Blade, Includes: 1/4 IN And 3/16 IN Slotted, #1 And #2 Phillips, 1/4 IN, 5/16 IN, 7/16 IN Nutdrivers, Ratcheting Screwdriver End, Ratcheting Wire Connector Wrench   |
| Product Type           | Screwdriver, Ideal, Ratch-A-Nut  |
| Special Features       | Ratcheting wire connector wrench prevents finger fatigue and gets in tight spots; Premium screwdriver ratchet mechanism can handle high torque without failure; Ergonomic, slip resistant comfort-grip; Textured Santoprene grip provides excellent torque and resists perspiration, water, oil and chemicals; Accepts Twist-a-Nut replacement bits; Pro-quality, 28 tooth double action, twin-tooth ratchet; 225 LB of torque (stronger than human wrist can torque)  |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Ideal          |
| GTIN                      | 00783250605224 |
| Manufacturers Part Number | 35-988         |
| UPC                       | 783250605224   |

## Taxonomies, Classifications, and Categories

|                      |                    |
|----------------------|--------------------|
| Category Description | HAND TOOLS         |
| Type                 | 9-In-1 Screwdriver |

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Weight Per each | 0.7 |