



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



370FSA 1" Alu Cond Body CVR Appleton/Oz Gedney

Catalog Number	370FSA
Manufacturer	Appleton/Oz Gedney
Description	FM7 Wedge-Lok Blank Clip Cover With Screw, Hub Size: 1 In, Form: 7, Mounting: Screw-In, Material: Cast Aluminum, Finish: Epoxy Powder Coat, Standard: UI 514A, UI 514B, UI File Number E2527, Csa C22.2 No. 18.3, Csa 065183, Nema FB-1, For FM
Weight per unit	0.2700 (lbs/each)
Product Category	Alum

Features

Form	7
Material	Cast Aluminum

Material, Color, and Finish

Finish	Epoxy Powder Coat
--------	-------------------

Dimensions and Weight

Hub Size	1
----------	---

Descriptions

Description	1" ALU COND BODY CVR
extra long description	APP 370FSA 1 IN FM7 COVER ALUM
Long Description	FM7 Wedge-Lok Blank Clip Cover With Screw, Hub Size: 1 IN, Form: 7, Mounting: Screw-In, Material: Cast Aluminum, Finish: Epoxy Powder Coat, Standard: UL 514A, UL 514B, UL File Number E2527, CSA C22.2 No. 18.3, CSA 065183, NEMA FB-1, For FM
Product Type	1 In FM7 Cover Alum
Special Features	Approved for use in wet locations;Stainless steel screws;The cover is secured with clips, not screws;Unique Wedge-Lok clip cover design allows easy removal without damaging the conduit body;Wiring capacity: 1.3 CU-IN as per NEC 314.16(A)

Manufacturer Information

Brand	Appleton
GTIN	00781381601283
Manufacturers Part Number	370FSA
UPC	781381601283

Taxonomies, Classifications, and Categories

Category Description	FORM 7, 8, CONDULETS, COVERS, & GASKETS
Type	Blank Clip Cover With Screw



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	100
Weight Per each	0.27

Uses, Certifications, and Standards

Application	For FM7 Unilet Conduit Outlet Bodies
Mounting	Screw-In
standard	UL 514A, UL 514B, UL File Number E2527, CSA C22.2 No. 18.3, CSA 065183, NEMA FB-1