

## E26 6" Trim Series

### DESCRIPTION

Open in the 6" trim family for use in recessed downlighting. Compatible for use in Halo and other housings.


Catalog #		Type
Project		
Comments		Date
Prepared by		

### SPECIFICATION FEATURES

- Open trim for BR40 and R40 lamps
- Coil spring retention

Housings	Max Lamp Compatibility	
H7T H7RT	120W BR40, 150W R40	
H7TCP		
E7TAT E7RTAT	120W BR40	

Compatible with Halogen, Incandescent, LED\* or CFL\* lamps.



**Dimensions:**  
OD: 8" [203mm]

### ORDERING INFORMATION

SAMPLE NUMBER: 401P

Trim	Finish
401P= 6" White Open Trim	WH=White Trim
401AL= 6" Satin Aluminum Open Trim	SA=Satin Aluminum

### HALO HOUSING COMPATIBILITY

Trim #	Style	H7ICT	H7ICAT	H7RICT	H7RICAT	E7ICAT	E7RICAT	H7UICAT	H7ICTNB
401P 401AL	Open								
		H7ICATNB	E7ICATNB	H27ICAT	H27RICAT	E27ICAT	E27RICAT		
		H7T	H7TCP	H7RT	E7TAT	E7RTAT	H7TNB	E7TATNB	H27T
		•	•	•	•	•			
		H27RT	E27TAT	E27RTAT					

For use in select other's housings, refer to U.L. classification list at [www.eaton.com/lighting/legal](http://www.eaton.com/lighting/legal).

\*UL1993 listed LED & CFL equivalent lamps permitted. Consult lamp manufacturer for conditions of use. Eaton does not warranty the lamp.



**401P**  
White Open Trim



**401AL**  
Satin Aluminum Open Trim

**401**

6-Inch Adjustable



For use in Halo listed housings.



Select trims are classified for use in others housings. See [www.eaton.com/lighting/legal](http://www.eaton.com/lighting/legal).

## E26 6" Trim Series

### DESCRIPTION

Open in the 6" trim family for use in recessed downlighting. Compatible for use in Halo and other housings.


Catalog #		Type
Project		
Comments		Date
Prepared by		

### SPECIFICATION FEATURES

- Open trim for BR40 and R40 lamps
- Coil spring retention

Housings	Max Lamp Compatibility	
H7T H7RT	120W BR40, 150W R40	
H7TCP		
E7TAT E7RTAT	120W BR40	

Compatible with Halogen, Incandescent, LED\* or CFL\* lamps.



**Dimensions:**  
OD: 8" [203mm]

### ORDERING INFORMATION

SAMPLE NUMBER: 401P

Trim	Finish
401P= 6" White Open Trim	WH=White Trim
401AL= 6" Satin Aluminum Open Trim	SA=Satin Aluminum

### HALO HOUSING COMPATIBILITY

Trim #	Style	H7ICT	H7ICAT	H7RICT	H7RICAT	E7ICAT	E7RICAT	H7UICAT	H7ICTNB
401P 401AL	Open								
		H7ICATNB	E7ICATNB	H27ICAT	H27RICAT	E27ICAT	E27RICAT		
		H7T	H7TCP	H7RT	E7TAT	E7RTAT	H7TNB	E7TATNB	H27T
		•	•	•	•	•			
		H27RT	E27TAT	E27RTAT					

For use in select other's housings, refer to U.L. classification list at [www.eaton.com/lighting/legal](http://www.eaton.com/lighting/legal).

\*UL1993 listed LED & CFL equivalent lamps permitted. Consult lamp manufacturer for conditions of use. Eaton does not warranty the lamp.



**401P**  
White Open Trim



**401AL**  
Satin Aluminum Open Trim

**401**

6-Inch Adjustable



For use in Halo listed housings.



Select trims are classified for use in others housings. See [www.eaton.com/lighting/legal](http://www.eaton.com/lighting/legal).