



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **44104 Wire Marker Booklet, Asst 46-90, 10 Each**

*Ideal*

|                  |                                                                                                                                                                                                                                                                                                                             |
|------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | 44104                                                                                                                                                                                                                                                                                                                       |
| Manufacturer     | Ideal                                                                                                                                                                                                                                                                                                                       |
| Description      | Ideal, Wire Marker Booklet, Size: 1/4 X 1-1/2 In Marker, Material: Plastic-Impregnated Cloth, Legend: 46-90, Temperature Rating: -40 to 180 Deg F, Markers Per Page: 10, Number Of Pages: 10/Booklet, Legend Color: Non-Smear Black, Adhesion: 45 Oz/In Width Ultimate, Includes: 450 Wire Markers and 450 Terminal Markers |
| Weight per unit  | 0.1400 (lbs/each)                                                                                                                                                                                                                                                                                                           |
| Product Category | Markers & Marking Tapes                                                                                                                                                                                                                                                                                                     |

### **Features**

|                 |                           |
|-----------------|---------------------------|
| Legend          | 46-90                     |
| Material        | Plastic-Impregnated Cloth |
| Number of Pages | 10/Booklet                |

### **Material, Color, and Finish**

|              |                 |
|--------------|-----------------|
| Legend Color | Non-Smear Black |
|--------------|-----------------|

### **Dimensions and Weight**

|      |                       |
|------|-----------------------|
| Size | 1/4 X 1-1/2 IN Marker |
|------|-----------------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description            | WIRE MARKER BOOKLET, ASST 46-90, 10 EACH                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| extra long description | IDEAL 44-104 Wire Marker Booklet,Id                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| Features               | Convenient pocket-size bookletsPlastic, cloth construction for long-lasting durabilityResist abrasion, moisture, dirt and oilPerforated 1/4 in. x 1-1/2 in. markers can be separated into half-length sizesNon-smear black legendSelf-sticking on wire and cableFor applications above or below groundTemperature Range: -40°F to 180°F (-40°C to 82°C)Adhesion: 45 oz./in. width ultimate                                                                                                  |
| Long Description       | IDEAL, Wire Marker Booklet, Size: 1/4 X 1-1/2 IN Marker, Material: Plastic-Impregnated Cloth, Legend: 46-90, Temperature Rating: -40 To 180 DEG F, Markers Per Page: 10, Number Of Pages: 10/Booklet, Legend Color: Non-Smear Black, Adhesion: 45 OZ/IN Width Ultimate, Includes: 450 Wire Markers And 450 Terminal Markers                                                                                                                                                                 |
| Product Type           | Wire Marker Booklet, Ideal, SZ: 1/4 X 1-1/2 In MRKR, Plastic-Im                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Special Features       | Features: Convenient Pocket-Size Booklets; Plastic-Impregnated Cloth Construction For Long-Lasting Durability; Resists Abrasion, Moisture, Dirt And Oil; Perforated 1-1/2 IN Markers Can Be Separated Into Half-Length Sizes; Self-Sticking On Wire And Cable; Non-Smear Black Legend Ensures High Visibility; For Applications Above Or Below Ground; Ten Pages Per Booklet, 10 Markers Per Legend; Adhesion: 45 OZ/IN Width Ultimate; Includes: 450 Wire Markers And 450 Terminal Markers |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Ideal          |
| GTIN                      | 00783250441044 |
| Manufacturers Part Number | 44-104         |
| UPC                       | 783250441044   |

## Taxonomies, Classifications, and Categories

|                      |                            |
|----------------------|----------------------------|
| Category Description | WIRE LUBE, MARKERS, & TIES |
|----------------------|----------------------------|

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 5    |
| Weight Per each | 0.14 |

## Uses, Certifications, and Standards

|                    |            |
|--------------------|------------|
| standard           | RoHS       |
| Temperature Rating | -40 To 180 |