



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 44148 Wire Marker Booklet, Solid A-Z, 45 Each

*Ideal*

|                  |   |
|------------------|---|
| Catalog Number   | 44148   |
| Manufacturer     | Ideal   |
| Description      | Ideal, Wire Marker Booklet, Size: 1/4 X 1-1/2 In Marker, Material: Plastic-Impregnated Cloth, Legend: A-Z, Temperature Rating: -40 to 180 Deg F, Markers Per Page: A-Z (45 Each), Number Of Pages: 26/Booklet, Legend Color: Non-Smear Black, Adhesion: 45 Oz/In Width Ultimate, Includes: 1170 Total Markers |
| Weight per unit  | 0.3000 (lbs/each)   |
| Product Category | Markers & Marking Tapes   |

### Features

|                 |                           |
|-----------------|---------------------------|
| Legend          | A-Z                       |
| Material        | Plastic-Impregnated Cloth |
| Number of Pages | 26/Booklet                |

### Material, Color, and Finish

|              |                 |
|--------------|-----------------|
| Legend Color | Non-Smear Black |
|--------------|-----------------|

### Dimensions and Weight

|      |                       |
|------|-----------------------|
| Size | 1/4 X 1-1/2 IN Marker |
|------|-----------------------|

### Descriptions

|                        |   |
|------------------------|---|
| Description            | WIRE MARKER BOOKLET, SOLID A-Z, 45 EACH   |
| extra long description | IDEAL 44-148 Wire Marker Booklet,Id   |
| Features               | Convenient pocket-size bookletsPlastic, cloth construction for long-lasting durabilityResist abrasion, moisture, dirt and oilPerforated 1/4 in. x 1-1/2 in. markers can be separated into half-length sizesNon-smear black legendSelf-sticking on wire and cableFor applications above or below groundTemperature Range: -40°F to 180°F (-40°C to 82°C)Adhesion: 45 oz./in. width ultimate                                |
| Long Description       | IDEAL, Wire Marker Booklet, Size: 1/4 X 1-1/2 IN Marker, Material: Plastic-Impregnated Cloth, Legend: A-Z, Temperature Rating: -40 To 180 DEG F, Markers Per Page: A-Z (45 each), Number Of Pages: 26/Booklet, Legend Color: Non-Smear Black, Adhesion: 45 OZ/IN Width Ultimate, Includes: 1170 Total Markers   |
| Product Type           | Wire Marker Booklet, Ideal, SZ: 1/4 X 1-1/2 In MRKR, Plastic-Im   |
| Special Features       | Features: Convenient Pocket-Size Booklets; Plastic-Impregnated Cloth Construction For Long-Lasting Durability; Resists Abrasion, Moisture, Dirt And Oil; Perforated 1-1/2 IN Markers Can Be Separated Into Half-Length Sizes; Self-Sticking On Wire And Cable; Non-Smear Black Legend Ensures High Visibility; 26 Pages Per Booklet, 45 Markers Per Page; Adhesion: 45 OZ/IN Width Ultimate; Includes: 1170 Total Markers |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Ideal          |
| GTIN                      | 00783250650798 |
| Manufacturers Part Number | 44-148         |
| UPC                       | 783250650798   |

## Taxonomies, Classifications, and Categories

|                      |                            |
|----------------------|----------------------------|
| Category Description | WIRE LUBE, MARKERS, & TIES |
|----------------------|----------------------------|

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 5   |
| Weight Per each | 0.3 |

## Uses, Certifications, and Standards

|                    |            |
|--------------------|------------|
| standard           | RoHS       |
| Temperature Rating | -40 To 180 |