



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 44900 Waypoint W/Mount and 12VDC Power Cord-Box - Yellow *Streamlight, Inc.*

|                  |  |
|------------------|--|
| Catalog Number   | 44900  |
| Manufacturer     | Streamlight, Inc.  |
| Description      | Spotlight, Non-Rechargeable, Hand Held, Pistol Grip Type; High Impact Polycarbonate Body Material; Led Lamp Type; (4) C Alkaline Battery Type; Yellow Body Color; Waypoint[R] Brand; Overall Dimension 6.75 Inch Length X 7.14 Inch Height |
| Weight per unit  | 0.5076 (lbs/each)  |
| Product Category | Flashlights, Lanterns, Warning   |

### Features

|              |                |
|--------------|----------------|
| Battery Type | (4) C Alkaline |
| Lamp Type    | LED            |

### Material, Color, and Finish

|               |                           |
|---------------|---------------------------|
| Body Color    | Yellow                    |
| Body Material | High Impact Polycarbonate |

### Descriptions

|                        |   |
|------------------------|---|
| Additional Information | Overall Dimension 6.75 Inch Length x 7.14 Inch Height; Head Diameter 3.5 Inch; Battery Run Time 82 Hour (Low), 10 Hour (High); Lamp Intensity 40 (Low), 550 (High) Lumen; Handle Type Rubberized Cushioned Grip; Includes Polycarbonate Len, O-Ring Sealed, 12  |
| Commodity Description  | FLASHLIGHTS,LANTERNS,WARNING LIGHTS   |
| Description            | WAYPOINT W/MOUNT AND 12VDC POWER CORD-BOX - YELLOW  |
| extra long description | PISTOL GRIP, NON-RECHARGEABLE TYPE; HIGH IMPACT POLYCARBONATE BODY MATERIAL; LED LAMP TYPE; (4) C ALKALINE BATTERY TYPE; YELLOW BODY COLOR; WAYPOINT[R] BRAND; ROHS COMPLIANT; HANDLE TYPE RUBBERIZED CUSHIONED GRIP; OVERALL DIMENSION 6.75 INCH LENGTH X 7.14 INCH HEIGHT; HEAD DIAMETER 3.5 INCH; BATTERY RUN TIME 82 HOUR (LOW), 10 HOUR (HIGH); LAMP INTENSITY 40 (LOW), 550 (HIGH) LUMEN; INCLUDES POLYCARBONATE LENS, O-RING SEALED, 12 VOLT DC POWER CORD |
| Long Description       | SPOTLIGHT, NON-RECHARGEABLE, HAND HELD, PISTOL GRIP TYPE; HIGH IMPACT POLYCARBONATE BODY MATERIAL; LED LAMP TYPE; (4) C ALKALINE BATTERY TYPE; YELLOW BODY COLOR; WAYPOINT[R] BRAND; OVERALL DIMENSION 6.75 INCH LENGTH X 7.14 INCH HEIGHT  |
| Product Type           | Spotlight   |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                   |
|---------------------------|-------------------|
| Brand                     | Streamlight, Inc. |
| GTIN                      | 00080926449008    |
| Manufacturers Part Number | 44900             |
| UPC                       | 080926449008      |

## Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | FLASHLIGHTS AND BATTERIES                |
| Type                 | Non-Rechargeable, Hand Held, Pistol Grip |

## Packaging

|                 |        |
|-----------------|--------|
| Carton          | 1      |
| Package         | 6      |
| Weight Per each | 0.5076 |