ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
5668 N. Hwy 81
73533-0000, OK Duncan
Phone: 580-252-2582
Fax: 580-252-2738



44931 The Siege, Coyote

Streamlight, Inc.

Catalog Number	44931
Manufacturer	Streamlight, Inc.
Description	Lantern, Floating, Waterproof Type; Tough Polycarbonate Thermoplastic Body Material; Led Lamp Type; (3) D Alkaline Battery Type; Coyote Body Color; No Battery Included; Siege[R] Brand; Rohs Compliant; Size 7.25" Height; Base Diameter 3.8"
Weight per unit	1.1 (lbs/each)
Product Category	Flashlights, Lanterns, Warning

Features

Battery Included	No
Battery Type	(3) D Alkaline
Lamp Type	LED

Material, Color, and Finish

Body Color	Coyote
Body Material	Tough Polycarbonate Thermoplastic

Descriptions

Additional Information	RoHS Compliant; Size 7.25" Height; Base Diameter 3.8"; Intensity 340 (High), 175 (Medium), 33 (Low) White LED, 10 (High), 10 (Flash/SOS Mode) Red LED; Includes Elastomer Over Mold, Rubber Molded Base; Warranty Lifetime Limited
Commodity Description	FLASHLIGHTS,LANTERNS,WARNING LIGHTS
Description	THE SIEGE, COYOTE
extra long description	COMPACT TYPE; RUGGED BODY MATERIAL; LED LAMP TYPE; (3) D ALKALINE BATTERY TYPE; COYOTE BODY COLOR; THE SIEGE[R] BRAND; ROHS COMPLIANT; SIZE 3.8 INCH X 7.25 INCH HAND; LAMP INTENSITY 540 LUMEN (HIGH)
Long Description	LANTERN, FLOATING, WATERPROOF TYPE; TOUGH POLYCARBONATE THERMOPLASTIC BODY MATERIAL; LED LAMP TYPE; (3) D ALKALINE BATTERY TYPE; COYOTE BODY COLOR; NO BATTERY INCLUDED; SIEGE[R] BRAND; ROHS COMPLIANT; SIZE 7.25" HEIGHT; BASE DIAMETER 3.8"
Product Type	Lantern

Manufacturer Information

Brand	Streamlight, Inc.
GTIN	00080926449312
Manufacturers Part Number	44931
UPC	080926449312

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
5668 N. Hwy 81
73533-0000, OK Duncan
Phone: 580-252-2582
Fax: 580-252-2738

Taxonomies, Classifications, and Categories

Category Description	FLASHLIGHTS AND BATTERIES
Type	Floating, Waterproof

Packaging

Carton	1
Package	6
Weight Per each	1.105