



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



4710 Turnlok SGL Recept 3W 15A 125V

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | 4710 |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Turnlok® Single Receptacle 3-Wire 15A 125a |
| Weight per unit | 0.1872 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|-----------------|-------------|
| amperage rating | 15 |
| Material | Nylon;Other |
| Number of Wires | 3 |
| Poles | Double Pole |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wire Size | 4 |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Black |
|-------|-------|

Dimensions and Weight

| | |
|------|------|
| Size | 4 in |
|------|------|

Descriptions

| | |
|------------------------|--|
| Description | TURNLOK SGL RECEPT 3W 15A 125V |
| extra long description | P&S 4710 TURNLOK SGL RECEPT 3W 15A |
| Long Description | Turnlok® Single Receptacle 3-Wire 15A 125A |
| Product Type | Turnlok SGL Recept 3W 15A 125V |
| Special Features | Locking Device, impact resistant |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007471007 |
| Manufacturers Part Number | 4710 |
| UPC | 785007471007 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------|
| Category Description | Industrial receptacles |
| Type | Turnlock Single Receptacle |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 10 |
| Package | 50 |
| Weight Per each | 0.1872 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|-----------------------|
| Application | Industrial Spec Grade |
| Mounting | Receptacle |
| nema rating | L5-15R |
| standard | CULUS, UL 498 |