



# M18 REDLITHIUM™

THE WORLD'S FIRST & ONLY 18V  
HIGH DEMAND™ 9.0 BATTERY

[Learn More](#)

Swap Banner



## 6" 24 TPI Thin Kerf SAWZALL® Blades (5 Pk)

48-00-5186



### Where to Buy



[Shop Online](#)



[Find Local](#)

### Features

- Optimized tooth design providing 2X more life than our previous generation SAWZALL® blades
- Tough Neck™ ribs strengthen the blade tang and minimize breakage
- Grid Iron™ honeycomb pattern increases blade rigidity to resist blade buckling.

### Specifications

<b>TPI</b>	24
<b>Length</b>	6.06"
<b>Profile</b>	Thin Kerf
<b>Pack Qty</b>	5 Pack
<b>Material</b>	EMT/Tube Duct/Sheet Metal

### Overview

Thin Kerf metal-cutting blades with the Double Duty Upgrade™ feature a tooth form that is optimized for the longest life and increased speed. Tough Neck™ is engineered to protect against tang breakage and delivers the strongest SAWZALL® blade tang on the market. Maintaining a short profile and thin body, these blades are ideal for making fast, flexible cuts.

### Model Options

Item/Cat #	TPI	Length	Profile	Pack Qty	
48-00-5090	10	4.04"	Thin Kerf	5 Pack	<a href="#">Shop Online</a> <a href="#">Find Local</a>

<b>Item/Cat #</b>	<b>TPI</b>	<b>Length</b>	<b>Profile</b>	<b>Pack Qty</b>	
48-00-5092	10	6.06"	Thin Kerf	5 Pack	Shop Online Find Local
48-00-5181	14	4.04"	Thin Kerf	5 Pack	Shop Online Find Local
48-00-5182	14	6.06"	Thin Kerf	5 Pack	Shop Online Find Local
48-00-5183	18	4.04"	Thin Kerf	5 Pack	Shop Online Find Local
48-00-5184	18	6.06"	Thin Kerf	5 Pack	Shop Online Find Local
48-00-5185	24	4.04"	Thin Kerf	5 Pack	Shop Online Find Local
48-00-5186	24	6.06"	Thin Kerf	5 Pack	Shop Online Find Local
48-00-5187	14	9.09"	Thin Kerf	5 Pack	Shop Online Find Local
48-00-5188	18	9.09"	Thin Kerf	5 Pack	Shop Online Find Local
48-00-5189	18	95.12"	Thin Kerf	5 Pack	Shop Online Find Local
48-00-8182	14	6.06"	Thin Kerf	25 Pack	Shop Online Find Local
48-00-8184	18	6.06"	Thin Kerf	25 Pack	Shop Online Find Local
48-00-8186	24	6.06"	Thin Kerf	25 Pack	Shop Online Find Local
48-01-2162	14	6.06"	Thin Kerf	10 Pack (Bulk)	Shop Online Find Local
48-01-2164	18	6.06"	Thin Kerf	10 Pack (Bulk)	Shop Online Find Local
48-01-2167	14	9.09"	Thin Kerf	10 Pack (Bulk)	Shop Online Find Local
48-01-2168	18	9.09"	Thin Kerf	10 Pack (Bulk)	Shop Online Find Local

<b>Item/Cat #</b>	<b>TPI</b>	<b>Length</b>	<b>Profile</b>	<b>Pack Qty</b>	
48-01-2169	18	95.12"	Thin Kerf	10 Pack (Bulk)	Shop Online Find Local
48-01-2182	14	6.06"	Thin Kerf	25 Pack (Bulk)	Shop Online Find Local
48-01-2184	18	6.06"	Thin Kerf	25 Pack (Bulk)	Shop Online Find Local
48-01-2186	24	6.06"	Thin Kerf	25 Pack (Bulk)	Shop Online Find Local
48-01-2187	14	9.09"	Thin Kerf	25 Pack (Bulk)	Shop Online Find Local
48-01-2188	18	9.09"	Thin Kerf	25 Pack (Bulk)	Shop Online Find Local
48-01-6182	14	6.06"	Thin Kerf	50 Pack	Shop Online Find Local
48-01-6184	18	6.06"	Thin Kerf	50 Pack	Shop Online Find Local
48-01-6186	24	6.06"	Thin Kerf	50 Pack	Shop Online Find Local
48-01-6187	14	9.09"	Thin Kerf	50 Pack	Shop Online Find Local
48-01-6188	18	9.09"	Thin Kerf	50 Pack	Shop Online Find Local
48-01-6189	18	95.12"	Thin Kerf	50 Pack	Shop Online Find Local
48-01-7092	10	6.06"	Thin Kerf	100 Pack (Bulk)	Shop Online Find Local
48-01-7182	14	6.06"	Thin Kerf	100 Pack (Bulk)	Shop Online Find Local
48-01-7184	18	6.06"	Thin Kerf	100 Pack (Bulk)	Shop Online Find Local
48-01-7186	24	6.06"	Thin Kerf	100 Pack (Bulk)	Shop Online Find Local
48-01-7187	14	9.09"	Thin Kerf	100 Pack (Bulk)	Shop Online Find Local
48-01-7188	18	9.09"	Thin Kerf	100 Pack (Bulk)	Shop Online Find Local

<b>Item/Cat #</b>	<b>TPI</b>	<b>Length</b>	<b>Profile</b>	<b>Pack Qty</b>	
48-01-7189	18	95.12"	Thin Kerf	100 Pack (Bulk)	Shop Online Find Local

---

© 2016 by Milwaukee Tool. All rights reserved.