



# 5 PC SDS PLUS M/2™ Kit

48-20-7490



## What's Included

- (1) 3/16" x 6" Rotary Hammer Drill Bit
- (1) 1/4" x 6" Rotary Hammer Drill Bits
- (1) 5/16" x 6" Rotary Hammer Drill Bit
- (1) 3/8" x 6" Rotary Hammer Drill Bit
- (1) 1/2" x 6" Rotary Hammer Drill Bit

## Where to Buy



Shop Online



Find Local

## Features

- 
- Enhanced Rebar Guards provide increased durability
- 
- Breaker Points lead to faster drilling speeds
- 
- Variable Flute for Up to 20% more Holes per Charge in Cordless Rotary Hammers
- 
- Centering Tip for exact spot drilling
- 
- Wear Mark Indicators to show end of life and when bit no longer meets the ANSI requirement
- 
- Reinforced Flutes for minimized vibration and maximum durability
- 

## Overview

Milwaukee® M/2™ 2-Cutter SDS-Plus Rotary Hammer Drill bits are the Most Durable 2-Cutter bits with up to 20% more holes per charge in cordless rotary hammers. The enhanced rebar guards provide increased durability in hard

## Specifications

<b>Length</b>	"
<b>Style</b>	SDS-PLUS
<b>Height</b>	1"
<b>Width</b>	1"

aggregate and rebar. Breaker Point pulverize the material more effectively resulting in faster drilling speeds. The variable flute allows for maximum debris extraction leading to up 20% more holes per charge in cordless rotary hammer

while making it a very durable bit in corded and cordless rotary hammers. Additionally, M/2™ features a centering tip for exact spot drilling, wear mark indicator indicating when the bit no longer meets ANSI diameter requirements, and a reinforced flute for durability and minimized vibration. The increased life and efficiency of the M/2™ 2-Cutter drill bit line provides the ideal solution in general concrete for cordless and corded rotary hammer users.

## Model Options

Item/Cat #	
5 PC SDS PLUS M/2™ Kit 48-20-7490	Shop Online Find Local
5 PC SDS Plus MX4™ Kit 48-20-7498	Shop Online Find Local
6 PC SDS PLUS MX4™ Kit 48-20-7499	Shop Online Find Local



# 5 PC SDS PLUS M/2™ Kit

48-20-7490



## What's Included

- (1) 3/16" x 6" Rotary Hammer Drill Bit
- (1) 1/4" x 6" Rotary Hammer Drill Bits
- (1) 5/16" x 6" Rotary Hammer Drill Bit
- (1) 3/8" x 6" Rotary Hammer Drill Bit
- (1) 1/2" x 6" Rotary Hammer Drill Bit

## Where to Buy

-  Shop Online
-  Find Local

## Features

- 
- Enhanced Rebar Guards provide increased durability
- 
- Breaker Points lead to faster drilling speeds
- 
- Variable Flute for Up to 20% more Holes per Charge in Cordless Rotary Hammers
- 
- Centering Tip for exact spot drilling
- 
- Wear Mark Indicators to show end of life and when bit no longer meets the ANSI requirement
- 
- Reinforced Flutes for minimized vibration and maximum durability
- 

## Overview

Milwaukee® M/2™ 2-Cutter SDS-Plus Rotary Hammer Drill bits are the Most Durable 2-Cutter bits with up to 20% more holes per charge in cordless rotary hammers. The enhanced rebar guards provide increased durability in hard

## Specifications

<b>Length</b>	"
<b>Style</b>	SDS-PLUS
<b>Height</b>	1"
<b>Width</b>	1"

aggregate and rebar. Breaker Point pulverize the material more effectively resulting in faster drilling speeds. The variable flute allows for maximum debris extraction leading to up 20% more holes per charge in cordless rotary hammer

while making it a very durable bit in corded and cordless rotary hammers. Additionally, M/2™ features a centering tip for exact spot drilling, wear mark indicator indicating when the bit no longer meets ANSI diameter requirements, and a reinforced flute for durability and minimized vibration. The increased life and efficiency of the M/2™ 2-Cutter drill bit line provides the ideal solution in general concrete for cordless and corded rotary hammer users.

## Model Options

Item/Cat #	
5 PC SDS PLUS M/2™ Kit 48-20-7490	<a href="#">Shop Online</a> <a href="#">Find Local</a>
5 PC SDS Plus MX4™ Kit 48-20-7498	<a href="#">Shop Online</a> <a href="#">Find Local</a>
6 PC SDS PLUS MX4™ Kit 48-20-7499	<a href="#">Shop Online</a> <a href="#">Find Local</a>