



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



48404070 5-3/8" Metal/Stainless Cutting Circular Saw Blade

Milwaukee Electric Tool

| | |
|------------------|---|
| Catalog Number | 48404070 |
| Manufacturer | Milwaukee Electric Tool |
| Description | Milwaukee Metal Circular Saw Blades Were Specifically Designed to Exceed The Expectations Of Contractors For Blade Life, Cut Quality, and Speed In The Most Demanding Metal Cutting Applications – Without A Lubricant. A Hand-Tensioned, Hardened Alloy Steel Body Extends Blade Life and Delivers The Highest Quality Cuts Available. Carbide Tipped Teeth With Alternate Top Bevel Grind Shear Through Metal Leaving Burr-Free, Cool-to-Touch Cuts. Designed For Use With The M18™ Cordless 5-3/8 In. Metal Saw, These Blade |
| Weight per unit | 0.4200 (lbs/each) |
| Product Category | Bits, Parts, Accessories |

Features

| | |
|-----------------------------|-------|
| Blade Diameter | 5 3/8 |
| idea granular category code | 1157 |

Dimensions and Weight

| | |
|------|-------|
| Size | 5-3/8 |
|------|-------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 5-3/8" METAL/STAINLESS CUTTING CIRCULAR SAW BLADE |
| extra long description | MILW 48-40-4070 5-3/8 in. Circular |
| Features | MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening, |
| Long Description | Milwaukee metal circular saw blades were specifically designed to exceed the expectations of contractors for blade life, cut quality, and speed in the most demanding metal cutting applications – without a lubricant. A hand-tensioned, hardened alloy steel body extends blade life and delivers the highest quality cuts available. Carbide tipped teeth with alternate top bevel grind shear through metal leaving burr-free, cool-to-touch cuts. Designed for use with the M18™ cordless 5-3/8 in. metal saw, these blade |
| Product Type | 5-3/8 In. Circular Saw Blade |
| Short Description | 5-3/8 in. Circular Saw Blade |
| Special Features | Dry - no lubricant required, saving time and money with less mess; Cool - no extreme heat buildup preserves blade life and allows handling the work piece immediately; Clean - no burrs eliminates secondary operations saving time and money; Lasts up to 25x longer than abrasive blades; A hand-tensioned, hardened alloy steel body extends blade life and delivers the highest quality cuts available; Carbide tipped teeth with Alternate Top Bevel grind shear through metal leaving burr-free, cool-to-touch cuts; Thin |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Milwaukee® |
| GTIN | 00045242233786 |
| Manufacturers Part Number | 48-40-4070 |
| UPC | 045242233786 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------|
| Category Description | BITS, BLADES, AND HOLE SAWS |
| Type | Circular Saw Blade |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 80 |
| Weight Per each | 0.42 |

Uses, Certifications, and Standards

| | |
|-------------|-------|
| Application | Metal |
|-------------|-------|