



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 4887 Conn 15A 125V 2P3W Vinyl STR YI

Eaton Wiring Devices

Catalog Number	4887
Manufacturer	Eaton Wiring Devices
Description	Eaton Arrow Hart Straight Blade Connector , #18-12 Awg, 15A, Commercial, 125V, Back Wire, Yellow, Brass, Vinyl, 5-15R, Two-Pole, Three-Wire, Grounding, Screw, 0.25-0.66", Vinyl, ED Box
Weight per unit	0.1600 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### Features

amperage rating	15
core	5-15R
dimensions	2.6000 IN X 1.5000 IN X 1.5000 IN
Material	Vinyl
Resistance	-20 to +60 C
Voltage Rating	5 +/-1 mA

### Material, Color, and Finish

Color	Black
Conductor Material	Copper
Insulation Material	PVC
Jacket Material	PVC

### Descriptions

Description	CONN 15A 125V 2P3W VINYL STR YL
extra long description	EWD 4887-BOX Conn 15A 125V 2P3W Vin
Features	Our compact yet rugged light commercial and standard residential grade plugs and connectors are available in a broad range of designs, materials and configurations for virtually any replacement application or do-it-yourself extension cord creation.
Long Description	Eaton Arrow Hart straight blade connector , #18-12 AWG, 15A, Commercial, 125V, Back wire, Yellow, Brass, Vinyl, 5-15R, Two-pole, three-wire, grounding, Screw, 0.25-0.66", Vinyl, ED Box
Product Type	Conn 15A 125V 2P3W Vinyl STR YI
Special Features	Spec grade plugs & conn

### Manufacturer Information

Brand	Southwire
GTIN	00032664341205
Manufacturers Part Number	4887-BOX
UPC	032664341205



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Residential cord connectors
Type	Straight Blade Connector

## Packaging

Carton	10
Package	100
Weight	0.15
Weight Per each	0.16

## Uses, Certifications, and Standards

Application standard	Extension Cord
Temperature Rating	UL817