



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



501I 15A 120/277VAC S Wire Comm SP SW Iv *Pass & Seymour/Legrand*

Catalog Number	501I
Manufacturer	Pass & Seymour/Legrand
Description	Commercial 1-Pole Switch, Side-Wire, 15A 120/277V.
Weight per unit	0.2100 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	Single pole
actuator	Toggle
amperage rating	15
Contact Rating	15amp, 120/277vac
indoor/outdoor	Indoor
insulation	False
Load Rating	15 A @ 120/277 VAC
Load Type	Universal, Halogen, Fluorescent, Xenon, Incandescent, LED, CFL
Material	Thermoplastic
media	Yes
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	1
Switch Type	Toggle
throw type	Single Throw
Voltage	120 VAC, 277 VAC
Voltage Rating	120/277
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	15A 120/277VAC S WIRE COMM SP SW IV
extra long description	P&S CS15AC1I 15A 120/277VAC S WIRE
Features	Single Piece Plated Steel Mounting Strap
Long Description	Commercial 1-Pole Switch, Side-Wire, 15A 120/277V.
Product Type	15A 120/277VAC S Wire Comm SP SW I
Special Features	Side wire, locking support, heavy duty toggle



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007126419
Manufacturers Part Number	CS15AC1I
UPC	785007126419

Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	SWITCH

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.21

Uses, Certifications, and Standards

Application	Commercial
Enclosure	Nylon
Mounting standard	WALL FEDSPEC, CULUS, UL 498/20, FEDSPEC