



HEAVY DUTY T-GRID BOX HANGER, MOUNTING CLIP

CATALOG NUMBER

512HD



CERTIFICATIONS



FEATURES

- Quickly mounts a box to T-grid
- Adjustable height for various electrical box depths
- Mounts flush with face of tile
- Installs by hand
- Drop wire for independent support from clip and/or bar
- Screws easily to tee bar for added stability
- Supports multiple box installations

PRODUCT ATTRIBUTES

- Material: Steel;Spring Steel
- Finish: Pregalvanized;nVent CADDY Armour
- Included Components: Mounting Clip
- Length: 24"

Box Depth: 1 1/4";2 1/8"

Ultimate Static Load: 50lb

ADDITIONAL PRODUCT DETAILS

Standard bar mounts 2 1/8" box. Break off tabs for 1 1/2" deep box. Mounts flush with face of tile.

512HDEEP Series with additional 512HDXT mounts 2 1/8" deep box with 1 1/2" extension ring.

Not permitted for paddle fans.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**
TRACER



HEAVY DUTY T-GRID BOX HANGER, MOUNTING CLIP

CATALOG NUMBER

512HD



CERTIFICATIONS



FEATURES

- Quickly mounts a box to T-grid
- Adjustable height for various electrical box depths
- Mounts flush with face of tile
- Installs by hand
- Drop wire for independent support from clip and/or bar
- Screws easily to tee bar for added stability
- Supports multiple box installations

PRODUCT ATTRIBUTES

- Material: Steel;Spring Steel
- Finish: Pregalvanized;nVent CADDY Armour
- Included Components: Mounting Clip
- Length: 24"

Box Depth: 1 1/4";2 1/8"

Ultimate Static Load: 50lb

ADDITIONAL PRODUCT DETAILS

Standard bar mounts 2 1/8" box. Break off tabs for 1 1/2" deep box. Mounts flush with face of tile.

512HDEEP Series with additional 512HDXT mounts 2 1/8" deep box with 1 1/2" extension ring.

Not permitted for paddle fans.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER

© 2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.