



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



52151MS1234 4\"/>

Abb Installation Products, Inc

| | |
|------------------|---|
| Catalog Number | 52151MS1234 |
| Manufacturer | Abb Installation Products, Inc |
| Description | Square Box, 21 Cubic Inches, 4 Inch Square X 1-1/2 Inch Deep, 1/2 Inch and 3/4 Inch Eccentric Knockouts, Pre-Galvanized Steel, MS Bracket, For Use With Conduit |
| Weight per unit | 0.8500 (lbs/each) |
| Product Category | Outlet Boxes, Etc. - Steel |

Features

| | |
|------------------|----|
| Knockouts | 12 |
| number of outlet | 1 |

Material, Color, and Finish

| | |
|-------|--------|
| Color | Silver |
|-------|--------|

Dimensions and Weight

| | |
|-------|-------|
| Depth | 1-1/2 |
|-------|-------|

Descriptions

| | |
|------------------------|---|
| Description | 4\"/> |
| extra long description | ABB 52151 MS 1/2 3/4 SQ BOX 21CU 1/ |
| Long Description | Square Box, 21 Cubic Inches, 4 Inch Square x 1-1/2 Inch Deep, 1/2 Inch and 3/4 Inch Eccentric Knockouts, Pre-Galvanized Steel, MS Bracket, for use with Conduit |
| Product Type | SQ Box 21CU 1/2 3/4IN E-Ko MS-BRKT |
| Special Features | Accepts all standard device covers and tile rings and is available in all box sizes and conduit styles |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Steel City |
| GTIN | 00785991165388 |
| Manufacturers Part Number | 52151 MS 1/2 3/4 |
| UPC | 785991165388 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | STEEL BOXES & COVERS |
| Type | Outlet Boxes |

Packaging

| | |
|-----------------|------|
| Carton | 25 |
| Weight Per each | 0.85 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|----------------------|
| Application | For use with conduit |
| standard | UL E2969 |