



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

204 Lake Road
76426-0000, TX Bridgeport
Phone: 940-683-5740
Fax: 940-683-5299



526321 5/8" SDS Plus Rotary Hammer Kit

Milwaukee Electric Tool

Catalog Number	526321
Manufacturer	Milwaukee Electric Tool
Description	The Most Compact 5/8 In. Hammer Drill On The Market Is 30% Lighter and 65% Faster – With Plenty Of Drilling Power. At Just 10.9 In. Long and 4.6 LBS., Milwaukee Tool 5/8 In. SDS-Plus Rotary Hammer Makes Drilling Overhead and In Tight Spaces Easier, Yet It'S Powerful Enough For Most Professional Applications. With A 5.5 Amp Motor, It Delivers 0-3, 700 RPM, 0-4, 400 BPM and 1.5 FT-LBS Of Torque. The Innovative Gear Design and A Drop Motor Provide Unmatched Balance, While Milwaukee'S Unique Anti-Vibration Syst
Weight per unit	9.0 (lbs/each)
Product Category	Power Tools - Corded

Features

amperage rating	5.5
Chuck Capacity	.625
Cord Length	10.0
Handle Type	D-Handle
idea granular category code	2302
Material	Mechanical Clutch; Metal Gear Box
Voltage	120.0

Dimensions and Weight

Height	5.0
Length	15
Width	12.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

204 Lake Road
76426-0000, TX Bridgeport
Phone: 940-683-5740
Fax: 940-683-5299

Descriptions

Description	5/8" SDS PLUS ROTARY HAMMER KIT
extra long description	MILW 5263-21 5263-21 RotaryHammer
Features	5/8 in. SDS Plus Rotary Hammer Kit
Long Description	The most compact 5/8 in. hammer drill on the market is 30% lighter and 65% faster – with plenty of drilling power. At just 10.9 in. long and 4.6 Lbs., Milwaukee Tool 5/8 in. SDS-Plus rotary hammer makes drilling overhead and in tight spaces easier, yet it's powerful enough for most professional applications. With a 5.5 amp motor, it delivers 0-3, 700 RPM, 0-4,400 bpm and 1.5 ft-lbs of torque. The innovative gear design and a drop motor provide unmatched balance, while Milwaukee's unique anti-vibration syst
Product Type	5263-21 Rotaryhammer
Short Description	5263-21 RotaryHammer
Special Features	Provides up to 65 PCT faster drilling speeds; Lightweight 4.6 LB design: Reduces fatigue when you drill overhead and in horizontal applications; Compact 10.9 IN profile: Lets you work more efficiently in tights spaces; 2-mode operation: Choose rotary hammer or rotation only for added versatility; Avs. anti-vibration system: Minimizes vibration for maximum comfort; Mechanical clutch: Protects the motor when the bit binds; The innovative gear design and a drop motor provide unmatched balance; Thin wall bit c

Manufacturer Information

Brand	Milwaukee®
GTIN	00045242192328
Manufacturers Part Number	5263-21
UPC	045242192328

Taxonomies, Classifications, and Categories

Category Description	POWER TOOLS
Type	SDS Plus Rotary Hammer Kit

Trade Size

Amperage	5.5
----------	-----

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Package	3
Weight Per each	8.995