



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

903 Mississippi Ave
76301-0000, TX Wichita Falls
Phone: 940-257-6832
Fax: 940-257-6833



5296BK Straight Blade Conn 3W 15A 125V Dead Front

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | 5296BK |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Straight Blade Connector 15A 125V Dead Front |
| Weight per unit | 0.1144 (lbs/each) |
| Product Category | Plugs, Connectors, Inlets, Out |

Features

| | |
|-----------------|----------------|
| amperage rating | 15 |
| connection | Wire Grounding |
| indoor/outdoor | Indoor |
| Material | Nylon |
| Number of Wires | 3.0 |
| Poles | 2 |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wire Size | 4 |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Black |
|-------|-------|

Dimensions and Weight

| | |
|------|--------|
| Size | 2.3 in |
|------|--------|

Descriptions

| | |
|------------------------|---|
| Description | STRAIGHT BLADE CONN 3W 15A 125V DEAD FRONT |
| extra long description | P&S 5296BK STR BLD CONN 3W 15A 125V |
| Features | Chemical Resistant |
| Long Description | Straight Blade Connector 15A 125V Dead Front |
| Product Type | STR BLD Conn 3W 15A 125V Dead Front |
| Special Features | Simple turn & twist assembly for quick installation |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007529616 |
| Manufacturers Part Number | 5296-BK |
| UPC | 785007529616 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------|
| Category Description | Residential cord connectors |
| Type | CONNECTOR |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

903 Mississippi Ave
76301-0000, TX Wichita Falls
Phone: 940-257-6832
Fax: 940-257-6833

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.1144 |

Uses, Certifications, and Standards

| | |
|-------------|-----------------------|
| Application | Stage & Entertainment |
| nema rating | 5-15R |
| standard | CSA, UL, UL 498 |