



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



60481612FD Encl 60X48X16 N12 FLRMT CH, 3PT LTCH *Cooper B-Line/Cable Tray*

Catalog Number	60481612FD
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Ground Mounted Panel Enclosure, 60" Height, 16" Length, 48" Width, Nema 12, Hinged Cover, 12FD Enclosure, Ground Mount, Large Double Door, Ground Mount Legs, Carbon Steel, Oil-Resistant Gasket
Weight per unit	361.6 (lbs/each)
Product Category	20130913101102

Features

dimensions	16.0000 IN X 48.0000 IN X 60.0000 IN
Mounting Type	Ground

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Size	48.00 In Width X 26.00 In Depth X 60.00 In Height
------	---

Descriptions

Description	ENCL 60X48X16 N12 FLRMT CH,3PT LTCH
extra long description	B-LINE 604816-12FD TYPE 12 DBL-DOOR
Features	Eaton's B-Line series JIC wall mount, ground mount and terminal Type 12 panel enclosures are used to house electrical controls and instruments while helping protect them against circulating dust, falling dirt and dripping non-corrosive liquids.
Long Description	Eaton B-Line series ground mounted panel enclosure, 60" height, 16" length, 48" width, NEMA 12, Hinged cover, 12FD enclosure, Ground mount, Large double door, Ground mount legs, Carbon steel, Oil-resistant gasket
Product Type	Type 12 DBL-Door Floor-Standing Enc, Less PNL, 60X48X16
Special Features	Plated door clamps

Manufacturer Information

Brand	Eaton
GTIN	00782051808001
Manufacturers Part Number	604816-12FD
UPC	782051808001

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Type 12 panel enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	361.6

Uses, Certifications, and Standards

Application	Stationary Mach Equip In Factory - RoboticsElec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMsUtility - Substations, Utility Transmission and DistributionWater and Wastewater Systems - Water and Wastewater Systems - OtherRail and Rail SystemsMobile Machinery and Equipment - Mobile Machinery and Equipment - Other
Mounting	Floor, Leg
standard	CSA C22.2, UL 508A, NEMA