

Specifications

Eaton 5S1500LCD

Eaton 5S UPS, 1500 VA, 900 W, 5-15P input,
Outputs: (10) 5-15R

General specifications

PRODUCT NAME	Eaton 5S UPS
CATALOG NUMBER	5S1500LCD
UPC	743172043566
PRODUCT LENGTH/DEPTH	15 in
PRODUCT HEIGHT	9.8 in
PRODUCT WIDTH	3.4 in
PRODUCT WEIGHT	25.5 lb
WARRANTY	3 year factory warranty with online product registration
COMPLIANCES	VCCI FCC Class B
CERTIFICATIONS	UL Listed NOM CSA Certified
PRODUCT TYPE	UPS

Battery

RUNTIME GRAPH [View runtime graph](#)

BATTERY MANAGEMENT

ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)

Electrical input

INPUT CONNECTION 5-15P

INPUT NOMINAL VOLTAGE 120V

INPUT CORD LENGTH 6 ft

INPUT VOLTAGE RANGE 93-138 Vac

INPUT FREQUENCY RANGE 46-70 Hz (50 Hz system);
57-70 Hz (60 Hz system)

Environmental

NOISE LEVEL <25 dB at 1 meter

TEMPERATURE RANGE 0° to 35°C (32° to 95°F)

RELATIVE HUMIDITY 0-93% non-condensing

Electrical output

BATTERY TYPE Sealed, lead-acid

RECEPTACLE (10) 5-15R

VA RATING 1500 VA

WATTAGE 900 W

OUTPUT NOMINAL VOLTAGE 100/120/127V

TOPOLOGY Line-interactive

Communications

COMMUNICATION USB HID port as standard,
6-ft USB cable included

SOFTWARE COMPATIBILITY Eaton UPS Companion software

Additional specifications

CONSTRUCTION TYPE Free standing model

PACKAGE CONTENTS

- UPS
- USB cable
- User manual
- Important safety instructions
- Limited warranty

COLOR Black

EFFICIENCY AT MAX. LOAD 95%

SURGE PROTECTION Yes

Warranty and support

STANDARD FACTORY WARRANTY

- 2-YEAR FACTORY WARRANTY
- -2 years
- -Parts, electronics, and batteries coverage
- -Standard ground shipping
- -Technical support

EXTENDED SERVICE PLANS

- ADVANCED DEPOT EXCHANGE
- -5-YEAR DEPOT REPAIR: 5SW5Y-1750UC
- -Expedited parts coverage for 5 years
- -Parts, electronics and UPS batteries coverage
- -Next business day shipping
- -Technical support

Resources

BROCHURES

[Eaton 5S UPS brochure](#)

[5-series UPS overview brochure](#)

MANUALS AND USER GUIDES

[Eaton 5S UPS safety manual](#)

[Eaton 5S UPS 120V user manual: 700, 1000, 1500 VA with LCD](#)

SPECIFICATIONS AND DATASHEETS

[Eaton 5S UPS technical specifications](#)

[Eaton Specification Sheet - 5S1500LCD](#)

WARRANTY GUIDES

[Eaton extended warranty certificate](#)

[Eaton limited warranty](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Eaton 5S1500LCD

Eaton 5S UPS, 1500 VA, 900 W, 5-15P input,
Outputs: (10) 5-15R

General specifications

PRODUCT NAME	Eaton 5S UPS
CATALOG NUMBER	5S1500LCD
UPC	743172043566
PRODUCT LENGTH/DEPTH	15 in
PRODUCT HEIGHT	9.8 in
PRODUCT WIDTH	3.4 in
PRODUCT WEIGHT	25.5 lb
WARRANTY	3 year factory warranty with online product registration
COMPLIANCES	VCCI FCC Class B
CERTIFICATIONS	UL Listed NOM CSA Certified
PRODUCT TYPE	UPS

Battery

RUNTIME GRAPH [View runtime graph](#)

BATTERY MANAGEMENT

ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)

Electrical input

INPUT CONNECTION 5-15P

INPUT NOMINAL VOLTAGE 120V

INPUT CORD LENGTH 6 ft

INPUT VOLTAGE RANGE 93-138 Vac

INPUT FREQUENCY RANGE 46-70 Hz (50 Hz system);
57-70 Hz (60 Hz system)

Environmental

NOISE LEVEL <25 dB at 1 meter

TEMPERATURE RANGE 0° to 35°C (32° to 95°F)

RELATIVE HUMIDITY 0-93% non-condensing

Electrical output

BATTERY TYPE Sealed, lead-acid

RECEPTACLE (10) 5-15R

VA RATING 1500 VA

WATTAGE 900 W

OUTPUT NOMINAL VOLTAGE 100/120/127V

TOPOLOGY Line-interactive

Communications

COMMUNICATION USB HID port as standard,
6-ft USB cable included

SOFTWARE COMPATIBILITY Eaton UPS Companion software

Additional specifications

CONSTRUCTION TYPE Free standing model

PACKAGE CONTENTS

- UPS
- USB cable
- User manual
- Important safety instructions
- Limited warranty

COLOR Black

EFFICIENCY AT MAX. LOAD 95%

SURGE PROTECTION Yes

Warranty and support

STANDARD FACTORY WARRANTY

- 2-YEAR FACTORY WARRANTY
- -2 years
- -Parts, electronics, and batteries coverage
- -Standard ground shipping
- -Technical support

EXTENDED SERVICE PLANS

- ADVANCED DEPOT EXCHANGE
- -5-YEAR DEPOT REPAIR: 5SW5Y-1750UC
- -Expedited parts coverage for 5 years
- -Parts, electronics and UPS batteries coverage
- -Next business day shipping
- -Technical support

Resources

BROCHURES

[Eaton 5S UPS brochure](#)

[5-series UPS overview brochure](#)

MANUALS AND USER GUIDES

[Eaton 5S UPS safety manual](#)

[Eaton 5S UPS 120V user manual: 700, 1000, 1500 VA with LCD](#)

SPECIFICATIONS AND DATASHEETS

[Eaton 5S UPS technical specifications](#)

[Eaton Specification Sheet - 5S1500LCD](#)

WARRANTY GUIDES

[Eaton extended warranty certificate](#)

[Eaton limited warranty](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

