



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



60406RL Full Brim Hard Hat W/ Rechargeable Headlamp, WH

Klein Tools

Catalog Number	60406RL
Manufacturer	Klein Tools
Description	Hard Hat, Non-Vented, Full Brim With Rechargeable Headlamp, White
Weight per unit	0.9000 (lbs/each)
Product Category	Tools & Testers

Features

battery life	Flood/Low Mode: 14 hr; Spot/High Mode 9 hr; Boost Mode: 4 hr
bulb type	LED
included	Hard Hat, Rechargeable Headlamp, Charging Cable, User Guide, Reflective Stickers
lumens	Boost: 300; Spot/High: 215; Flood/Low: 100
Material	PC/ABS
media	Yes
Overall Height	6.5" (16.5 cm)
Overall Width	10.7" (27.2 cm)

Material, Color, and Finish

Shell Material	PC/ABS
----------------	--------

Dimensions and Weight

Overall Length	12.5" (31.8 cm)
----------------	-----------------

Descriptions

Description	FULL BRIM HARD HAT W/ RECHARGEABLE HEADLAMP, WH
extra long description	KLEIN 60406RL Hard Hat, Non-vented
Long Description	Hard Hat, Non-Vented, Full Brim with Rechargeable Headlamp, White
Product Type	Hard Hat, Non-Vented Brim, Headlamp
Special Features	Tested up to 20kV

Manufacturer Information

Brand	Klein Tools
GTIN	00092644604270
Manufacturers Part Number	60406RL
UPC	092644604270

Taxonomies, Classifications, and Categories

Category Description	SAFETY PRODUCTS
Type	Type 1



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight	1.3 lb (0.6 kg)
Weight Per each	0.9

Uses, Certifications, and Standards

Application	Class E
Configuration	Hard Hat w/Rechargeable Light
standard	ANSI Z89.1-2014, CSA Z94.1-15, EN397:2012+A1:2012-Lateral Deformation (LD); EN12492:2012-4.2.1.2, 4.2.1.3, 4.2.1.4