



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



60406RL Full Brim Hard Hat W/ Rechargeable Headlamp, WH

Klein Tools

Catalog Number	60406RL
Manufacturer	Klein Tools
Description	Hard Hat, Non-Vented, Full Brim With Rechargeable Headlamp, White
Weight per unit	0.9000 (lbs/each)
Product Category	Tools & Testers

Features

battery life	Flood/Low Mode: 14 hr; Spot/High Mode 9 hr; Boost Mode: 4 hr
bulb type	LED
included	Hard Hat, Rechargeable Headlamp, Charging Cable, User Guide, Reflective Stickers
lumens	Boost: 300; Spot/High: 215; Flood/Low: 100
Material	PC/ABS
media	Yes
Overall Height	6.5" (16.5 cm)
Overall Width	10.7" (27.2 cm)

Material, Color, and Finish

Shell Material	PC/ABS
----------------	--------

Dimensions and Weight

Overall Length	12.5" (31.8 cm)
----------------	-----------------

Descriptions

Description	FULL BRIM HARD HAT W/ RECHARGEABLE HEADLAMP, WH
extra long description	KLEIN 60406RL Hard Hat, Non-vented
Long Description	Hard Hat, Non-Vented, Full Brim with Rechargeable Headlamp, White
Product Type	Hard Hat, Non-Vented Brim, Headlamp
Special Features	Tested up to 20kV

Manufacturer Information

Brand	Klein Tools
GTIN	00092644604270
Manufacturers Part Number	60406RL
UPC	092644604270

Taxonomies, Classifications, and Categories

Category Description	Job Site & Safety Apparel
Type	Type 1



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight	1.3 lb (0.6 kg)
Weight Per each	0.9

Uses, Certifications, and Standards

Application	Class E
Configuration	Hard Hat w/Rechargeable Light
standard	ANSI Z89.1-2014, CSA Z94.1-15, EN397:2012+A1:2012-Lateral Deformation (LD); EN12492:2012-4.2.1.2, 4.2.1.3, 4.2.1.4