



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



65217 Security Light W/Sensor White 4000K

Satco

| | |
|------------------|---|
| Catalog Number | 65217 |
| Manufacturer | Satco |
| Description | Led Security Light - Dual Head White Finish 4000K Motion Sensor |
| Weight per unit | 2.8 (lbs/each) |
| Product Category | Security Lights |

Features

| | |
|-----------------|---------------------------|
| Ballast Type | Self |
| Lamp Type | Light |
| Material | Die Cast Aluminum |
| Number of Lamps | 2 |
| Socket Type | Hardwired |
| Voltage Rating | 120 |
| Warranty | 5 Year Limited - Fixtures |
| Wattage | 20 |

Material, Color, and Finish

| | |
|------------------|-------------------|
| fixture material | Die Cast Aluminum |
| Style | Commercial |

Dimensions and Weight

| | |
|--------|------|
| Height | 7.63 |
| Length | 7.63 |
| Width | 4.16 |

Descriptions

| | |
|------------------------|---|
| Description | SECURITY LIGHT W/SENSOR WHITE 4000K |
| extra long description | SATCO 65/217 LED DUAL HEAD SECURITY |
| Long Description | LED Security Light - Dual Head White Finish 4000K Motion Sensor |
| Product Type | Led Dual Head Security Light WH 4K MS |
| Special Features | Lawful for sale in California ; California T24 Compliant ; Non-Dimmable ; Energy Star: Yes ; IP Rating: IP65 ; Lumens: 1900 ; Operating Temperature: -30C (-22F) to a maximum of +50C (+122F) ; Photocell: Has Motion Sensor ; Replaceable Light Source: No ; RoHS compliant ; Fixture Material: Die-cast aluminum ; Shade Material: Glass ; CRI: 80 ; Color Temperature: 4000K ; Beam Angle: 50 degrees ; 50000 average rated hours of use ; 5 Year Limited Warranty |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Nuvo |
| GTIN | 00045923680373 |
| Manufacturers Part Number | 65/217 |
| UPC | 045923680373 |

Taxonomies, Classifications, and Categories

| | |
|------|----------|
| Type | Fixtures |
|------|----------|

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight | 2.8 |
| Weight Per each | 2.8 |

Uses, Certifications, and Standards

| | |
|--------------------------------|--|
| Application | Outdoors |
| Operating Temperature standard | -30C (-22F) to a maximum of +50C (+122F) cULus Wet Listed |