



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



68RCSTBRN BRN Round Recessed Floor Box Cover

Abb Installation Products, Inc

Catalog Number	68RCSTBRN
Manufacturer	Abb Installation Products, Inc
Description	Recessed Service Floor Box Cover Kit, Accepts Duplex Receptacles GFI Receptacles and 2 Port Keystone Data Plate, Brown, Non-Metallic, For Use With Flush Service Floor Box, 100 Cubic Inches, Opening Diameter 5-5/32 Inches, Base Diameter 6-3/8 Inches, Depth 6 Inches, 3/4 Inch and 1 Inch Conduit Tapping, Plastic, For Power or Communications/Data and Wood Sub-Floor and Raised Floor Applications
Weight per unit	1.5 (lbs/each)
Product Category	Floor Boxes & Accessories

Features

Knockouts	FALSE
Material	Non-Metallic

Material, Color, and Finish

Color	Brown
-------	-------

Descriptions

Description	BRN ROUND RECESSED FLOOR BOX COVER
extra long description	ABB 68R-CST-BRN ROUND RECESSED COVE
Long Description	Recessed Service Floor Box Cover Kit, Accepts Duplex Receptacles GFI Receptacles and 2 Port Keystone Data Plate, Brown, Non-Metallic, For use with Flush Service Floor Box, 100 Cubic Inches, Opening Diameter 5-5/32 Inches, Base Diameter 6-3/8 Inches, Depth 6 Inches, 3/4 Inch and 1 Inch Conduit Tapping, Plastic, For Power or Communications/Data and Wood Sub-Floor and Raised Floor Applications
Product Type	Round Recessed Cover - Brown
Special Features	Unique cover provides aesthetic recessed service

Manufacturer Information

Brand	Steel City
GTIN	00785991044423
Manufacturers Part Number	68R-CST-BRN
UPC	785991044423

Taxonomies, Classifications, and Categories

Category Description	FLOOR BOXES
Type	Flush Service



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	4
Weight Per each	1.49

Uses, Certifications, and Standards

Application	For use with 68 P round floor box
standard	UL E11461 / UL E11461